



Thermal Transfer Printers

TT130SMC Compact Thermal Transfer Printer

Designed with space and portability in mind, the TT130SMC thermal transfer printer's compact footprint allows for highly efficient printing in applications in which space is tight or when portability is important. The smaller size and optional hard-shell carrying case make it easy to transport to remote job sites. The printer accommodates label roll stock up to 2" wide, to satisfy most solar installation labeling requirements. The TT130SMC includes an Ethernet port that allows the user to connect to an existing network or to a wireless router for portable printing. For ultimate print efficiency and workflow management, users can connect several TT130SMC printers together and use TagPrint® Pro label software or the TagPrint® Xpress mobile application to create a multiple printer network. The TT130SMC also comes with a label "caddy" to hold larger label rolls. The carrying case includes space for two printers, as well as a wireless router, cables and label stock.



TT130SMCKIT

Material Data	
Dimensions of printer	Width - 5.50" (140 mm) Height - 6.98" (177 mm) Depth - 11.0" (241 mm)
Weight	5.6 lbs (2.54 kg)
Power supply	100-240V Output: DC 24V 2.5A
Operation temperature	+50F to +95F (+10C to +35C)
Print density	300 dpi
Media diameter	Total diameter - 8.27" (210 mm) Core diameter - 3.0" (76.2 mm) Winding direction - Inside or outside
Material thickness	.0028" - .007" (.06 mm - .19 mm)
Operating system	Windows 2000 / XP / Vista / 7 / 8

Features & Benefits

- Lightweight, compact design makes it easy to transport to remote job sites
- Connect several printers together for ultimate printing efficiency
- 300 dpi print head for quality print results
- Fast print speed up to 2.3" (58.42mm) / second
- Easy to set up and load
- Label caddy holds larger rolls
- Highly accurate sensor reduces label waste
- Includes USB 2.0 port and Ethernet port for connection to network or wireless router
- 4mb flash / 8mb SDRAM
- Approvals; CE, FCC, Class A, cULus, UL, GS, TUV-GS, LCC, C-Tick, BSMI, RoHS

Product Selection				
Article No.	Part No.	Type	Description	Pkg. Qty
556-00250	556-00250	TT130SMC	TT130SMC Printer with Cutter	1
556-00254	556-00254	TT130SMCKIT	TT130SMC Printer Kit*	1
556-00257	556-00257	2TT130SMCKIT	2 Printer TT130SMC Printer Kit**	1
556-00251	556-00251	TT130RPHEAD	TT130SMC Print Head	1
556-00252	556-00252	TT130PWRSPLY	TT130SMC Power Supply	1
556-00255	556-00255	TT130SMCCORD	TT130SMC Replacement Power Cord	1
556-00253	556-00253	TT130SMCCASE	Optional Carrying Case	1
556-00235	556-00235	Label Holder	Replacement Label Holder	1
556-00205	556-00205	TTWHITEOUTSM-2	White Ribbon 2" X 154', 1/RL	1
556-00206	556-00206	TT822OUTSM-2	Black Ribbon 2" X 242', 1/RL	1

*Includes the TT130SMC printer with cutter, TagPrint® Pro 3.0 software, black and white ribbon, caddy and hard-shell carrying case.

**Includes two (2) TT130SMC printers with cutter, TagPrint Pro 3.0 software, (2) black ribbon, (2) white ribbon, (2) caddies and (1) hard-shell carrying case.

Printing Specifications

- Prints on media up to 2" (50.8 mm) wide.
- Uses 1/2" core HellermannTyton ribbons.
- Maximum print width - 2.13" (54.1 mm)
- Minimum print width - .59" (15.0 mm)