




AVAILABLE IN 2 COLORS | WHITE: White Bezel w/ White Front
BLACK: Black Bezel w/ Black Front (shown)


MODEL #		VZ-PVM-Z4B3	
DISPLAY			
Screen Size	32"		
Max. Resolution	1920x1080 @60Hz		
Pixel Pitch	0.36375mm x 0.36375mm		
Brightness	350cd/m ² (Typical)		
Contrast Ratio	3000:1		
Aspect Ratio	16:9		
Viewing Angle (H/V)	178°/178°		
Display Color	16.7 Million		
Response Time	<6.5ms		
Video System	NTSC / PAL		
Frequency (H/V)	31~80KHz / 56~75Hz		
INTERFACE			
AV(Composite) In/ Out	1 / 1		
Camera Out	1		
DVI-In / HDMI In / RGB In(15Pin D-Sub)	1 / 2 / 1		
PC Stereo In/Speak Out	1 / 1		
SPECIAL FEATURES			
Multi Display Function	PIP / PBP / VOV		
Filter Type	3D Comb-filter / DeInterlace		
Video Resolution(Max)	600 TV Line		
Multi-lingual Language	English, French, Deutsch, Italian, Spanish, Portuguese, Nederland		
DIMENSIONS			
Outline Dimension	28.86" x 20.52" x 3.58"		
(W x H x D)	(733mm x 521.2mm x 91mm)		
Net Weight	36.82 lbs (16.7kg)		
MOUNT			
VESA	200mm x 200mm, M6x8 Screws		
CAMERA			
Camera Type	Mega Pixel Camera		
Image Sensor	Panasonic 1.3 Mega Pixel C-MOS Sensor		
Lens	DC Auto Iris 3.6~16mm Vari-focal Lens		
Total / Effect Pixel	1280(H) x 720p(V) 60p		
MEDIA CARD			
Support Type	Photo, Music, Video		
Support File Format	MPEG1, MPEG4, JPEG, BMP, GIF, PNG, MP3		
Memory - Internal	512MB Nand Flash		
- External	USB1.1, USB2.0, SD(4in1):SD/MMC/MS/XD		
Resolution	720 X 576		
GENERAL			
Transmitter - IR Remote Control	YES		
Power - Electrical Ratings	110V AC (50/60Hz)	24V DC	
- Consumption	0.6 A (66W)	2.8 A (66W)	
Warranty - Parts/ Labor	3 Year / 3 Year		
- MTBF (Approx.)	50,000 Hours		
Operating Temperature	32 - 104°F / 0 - 40°C		
Regulations	TUV-NRTL (=UL), FCC(A)		
Compatible Mounts - WALL	VZ-AM02, VZ-WM50		
- CEILING	VZ-CMK01, VZ-CMK02, VZ-CMK03		

VZ-PVM-Z4B3 ADVANTAGES:

- 32" Public View Monitor
- Commercial grade LED
- Built in 1.3 Mega Pixel Camera
- Camera Motion Sensor
- Support dual voltage solution (110V AC and 24V DC)
- 3D Comb-filter, De-interlace
- 3-Year Warranty



INTERFACE



1. HDMI2 IN
2. HDMI1 IN
3. VGA IN
4. DVI IN
5. PC STEREO IN/AUDIO OUT
6. CAMERA OUT
7. AV(composite)2 IN/OUT
8. MEDIA CARD(USB, SD) - Optional
9. AC110V IN
10. DC 24V IN

Contact ViewZ

- Address: 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone: (714) 996-1177, Fax: (714) 996-1138
- Sales: sales@viewzusa.com
- Specifications subject to change without notice.