




MODEL #		VZ-46UNL
VIDEO		
Screen Size	46"	
Max. Resolution	1920 x 1080 @60Hz	
Pixel Pitch	0.53025mm x 0.53025mm	
Brightness	500cd/m ² (Typical)	
Contrast Ratio	3500:1	
Aspect Ratio	16 : 9	
Viewing Angle (H/V)	178° / 178°	
Display Color	16.7 Million	
Response Time	< 8ms	
Video System	NTSC / PAL	
Frequency (H)	31 ~ 80Khz	
Frequency (V)	56 ~ 75Hz	
INTERFACE		
VGA In (15Pin D-Sub)	1	
DVI-D In	1	
HDMI In	1	
RJ-45 In	1	
PC Stereo In / Out	1 / 1	
AUDIO		
Built in speaker	2W X 2	
SPECIAL FEATURES		
Bezel Width	TOP and LEFT Side	0.118" / 3 mm
	BOTTOM and RIGHT Side	0.114" / 2.9 mm
	ACTIVE AREA to ACTIVE AREA	0.232" / 5.9 mm
RS-232 / RJ-45 Control Program	Monitor OSD	
Image Rotation	YES	
Rotate IR receiver	YES	
Multi-lingual Language	English, Spanish, French, German, Italian, Portuguese, Dutch	
DIMENSIONS & WEIGHT		
Outline Dimension (W x H x D)	40.31" x 22.78" x 5.41" (1023.98mm x 578.70mm x 137.40mm)	
Net Weight	30.3kg / 66.80 lbs	
MOUNT		
VESA	600 x 100 x 100 x 100mm, M8x12 Screws	
GENERAL		
Transmitter - IR Remote Control	YES	
Power	Electrical Ratings	AC100 ~ 240V(50/60Hz)
	Consumption	240 W
Warranty	Parts/ Labor	3 Year / 3 Year
	MTBF (Approx.)	50,000 Hours
Operating Temperature	32 - 104°F / 0 - 40°C	
Compatible Mounts	VZ-XM46	


VZ-46UNL ADVANTAGES

- 46" 1080p CCTV LED Monitor
- Ultra Narrow 3mm Metal Bezel
- Video Wall Construction - Active to Active Bezel Width 5.9 mm
- OSD Function Control through RJ-45 protocol
- Digital & Analog Inputs, 3-Year Warranty
- Image Rotation Feature Prevents "Pixel Burn-In"

DIMENSIONS



INTERFACE



1. AC 110V IN
2. RJ-45 IN
3. PC STEREO IN/OUT
4. VGA IN
5. DVI-D IN
6. HDMI IN

Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.