



1x8 VGA Splitter with Audio High Bandwidth 1080p



CDA-VGA108A is a high resolution 1X8 VGA splitter with stereo audio. It distributes the input of the VGA signal and stereo audio signal into eight identical outputs simultaneously. The CDA-VGA108A has up to 500 Mhz bandwidth for the most demanding applications and buffers and amplifies the signal to ensure signal integrity from both outputs. Each amplifier splitter's output can achieve long distance transmission of VGA signal of more than 15 meters and longer with premium Comprehensive cables. The CDA-VGA105A durable metal construction is perfect for commercial or residential applications including conference room presentations, school and corporate training environments, data centers, home office and more. 2 Year warranty.

Features

- Splits One VGA and Stereo Audio Input to Eight (8) Outputs
- Buffered Amplification for Longer Distance Transmission
- Up to 1920x1200 and 1080p Resolution
- 500 Mhz Bandwidth
- Metal Enclosure
- 2 Year Warranty

Specifications

Input: 1 VGA 15pin male, 1 3.5mm Stereo Mini Female
Output: 8 VGA 15pin female, 8 3.5mm Stereo Mini Female
Input video Signal: 1.2 volts p-p
Maximum Single Link Range: 1920x1200, 1080p
Vertical Frequency Range: 30-170Hz
Video Amplifier Bandwidth: 500MHz
Size(L-W-H): 120x71x24.5mm
Weight: 930g, 2 Lbs.
Warranty: 2 Years
Operating Temperature: 0°C to +70°C

Operating Humidity: 10% to 85 % RH (no condensation)
Storage Temperature: -10°C to +80°C
Storage Humidity: 5% to 90 % RH (no condensation)
Power Requirement: External Power Supply 5V DC@2A
Power consumption (Max): 5W(max)
Regulatory Approvals: FCC, CE, UL

CDA-VGA108A - 1x8 VGA Splitter with Audio High Bandwidth 1080p