



## DVI Extender over single CAT5 cable up to 164ft (50m)



The Comprehensive CE-DVISM is a DVI over CAT5 extender over single CAT5 cable up to 70 meters/230ft. The unit is passive, no external power is required. The CE-DVISM is sold as a pair and uses one CAT5/5e/6 cable to send the DVIDVI signal. Extend the transmission distance up to 70 meters at 1024x768. Extend the transmission distance up to 50 meters at 1920x1200. Unit comes with a 2 year warranty.

### Features

- Includes transmitter and receiver, used in pairs via one CAT5e/6 cable to send DVI signal
- Active receiver for high performance
- No external power required
- Support high resolution up to 1920 x 1200
- Support long distance up to 70 meters at 1024x768
- Does not support HDCP

### Specifications

DVI Connector: 1xDVI-D 29 pin  
Link Connector: 1xRJ-45 Shielded  
Video Bandwidth: 1.65 Gbps ( DVI 1.1)  
Resolution: Up to 1920 x 1200 @60hz  
Does not support HDCP  
Input TMDS Video Signal: 1.2 volts p-p

Input DDC Signal: 5 volts p-p (TTL)  
Link Cable Distance: 65M@1024x768, 50M@1920x1200  
Temperature Operation: 0 to 55 C, Storage: -20 TO 85 C,  
Humidity: up to 95%  
Dimensions: W x H x D mm: 40 x 56 x 24.5  
Weight: 50g, 0.2 lb.  
Warranty: 2 Years

**CE-DVISM** - DVI Extender over single CAT5 cable up to 164ft (50m)