



USB 2.0 A to A Cable

USB (Universal Serial Bus) cables provide digital signal transmission rates of up to 480Mbps. USB Cables are commonly used to connect computers and peripherals such as printers, scanners, cameras, keyboards, mice and other digital devices. Comprehensive USB cables are premium shielded twisted pair construction for superior signal transfer. These cables are USB 2.0 and backwards compatible for USB 1.0 and 1.1. RoHS Compliant. Lifetime Warranty.



Features

- USB Type A Male to Type A Male
- Transfer rates up to 480Mbps
- Premium shielded twisted pair construction
- Plug and play functionality for printers, scanners, keyboards and other digital devices
- PC and Mac compatible
- Compatible with USB specifications 1.0, 1.1, and 2.0
- Molded Strain Relief
- RoHS Compliant
- Lifetime Warranty

- USB2-AA-3ST** - 3ft.
- USB2-AA-6ST** - 6ft.
- USB2-AA-10ST** - 10ft.
- USB2-AA-15ST** - 15ft.
- USB2-AA-25ST** - 25ft.

Specifications

Performance Grade: Good
 Connector Type 1: USB A Male
 Connector Type 2: USB A Male
 Bandwidth or Speed: Supports Hi-Speed, 480 Mbps
 Gauge: 28AWG
 Center Conductor: Tinned Copper
 Connector Finish: Nickel
 Shielding: 65% Braid
 UL Rated: Yes
 UL Rating: VW-1
 Ferrite Cores: No
 RoHS Compliant: Yes
 Jacket Type: Xtra-Flex PVC
 Jacket Color: Black
 Temperature Rating: 80 deg C
 Voltage: 30V
 Warranty: Lifetime
 Weight Lbs: 0.2

USB ADAPTERS