



## Standard Series USB 2.0 A to Mini B 5 pin Cable

USB (Universal Serial Bus) cables provide digital signal transmission rates of up to 480Mbps. USB Cables are commonly used to connect computers and peripherals such as printers, scanners, cameras, keyboards, mice and other digital devices. Comprehensive USB cables are premium shielded twisted pair construction for superior signal transfer. These cables are USB 2.0 and backwards compatible for USB 1.0 and 1.1. RoHS Compliant. Lifetime Warranty.



### Features

- USB Type A Male to Type B Male
- Transfer rates up to 480Mbps
- Premium shielded twisted pair construction
- Plug and play functionality for printers, scanners, keyboards and other digital devices
- PC and Mac compatible
- Compatible with USB specifications 1.0, 1.1, and 2.0
- Molded Strain Relief
- RoHS Compliant
- Lifetime Warranty



### Specifications

Performance Grade: Good  
 Connector Type 1: USB A Male  
 Connector Type 2: USB Mini B 5 Pin Male  
 Bandwidth or Speed: Supports Hi-Speed, 480 Mbps  
 Gauge: 28AWG  
 Center Conductor: Tinned Copper  
 Connector Finish: Nickel  
 Shielding: 65% Braid  
 UL Rated: Yes

UL Rating: VW-1  
 Ferrite Cores: No  
 RoHS Compliant: Yes  
 Jacket Type: Xtra-Flex PVC  
 Jacket Color: Black  
 Temperature Rating: 80 deg C  
 Voltage: 30V  
 Warranty: Lifetime

USB CABLES

<b>USB2-A-MB-3ST</b>	3ft.
<b>USB2-A-MB-6ST</b>	6ft.
<b>USB2-A-MB-10ST</b>	10ft.
<b>USB2-A-MB-25ST</b>	25ft.