



## Standard Series USB 2.0 A to Micro B Cable

This 3' USB A to Micro USB B Cable provides one USB A Male connector, and one Micro USB B connector to create a simple way to connect mobile devices to a USB capable computer for every day tasks such as data synchronization and file transfers.



### Features

- Premium Construction
- Molded strain relief
- X-traflex jacket
- Lifetime Warranty



### Specifications

Performance Grade: Good  
 Connector Type 1: USB A Male  
 Connector Type 2: USB Micro B Male  
 Bandwidth or Speed: Supports Hi-Speed, 480 Mbps  
 Gauge: 28AWG  
 Center Conductor: Tinned Copper  
 Connector Finish: Nickel  
 Shielding: 65% Braid  
 UL Rated: Yes

UL Rating: VW-1  
 Ferrite Cores: No  
 RoHS Compliant: Yes  
 Jacket Type: Xtra-Flex PVC  
 Jacket Color: Black  
 Temperature Rating: 80 deg C  
 Voltage: 30V  
 Warranty: Lifetime

<b>USB2-A-MCB-3ST</b>	3ft.
<b>USB2-A-MCB-6ST</b>	6ft.
<b>USB2-A-MCB-10ST</b>	10ft.