



Pro AV/IT Active Plenum USB A Male to A Female Cable

Comprehensive Active Pro AV/IT Plenum USB Extender Cables eliminate the 15ft USB length constraint allowing for extended USB connections. This active USB A male to A female cable allows placement of USB devices up to 75 feet away. Cable uses a center position booster to allow for placement behind wall plates as you can add up to 15 feet to either end of this cable. This extension cable actively buffers the incoming and outgoing signals to ensure compliance with the USB 2.0 specification for electrical and timing minimums. Designed for use with USB 2.0 or 1.1 devices including webcams, interactive whiteboards, and printers. Molded strain relief provides unsurpassed durability. A plenum rated jacket allows insallation in ceilings without using conduit. Lifetime Warranty.

Features

- Professional grade heavy-duty construction
- USB A Male to USB A Female
- USB 2.0 compliant up to 480mbps, backward compatible with USB 1.0 standards
- No external power required (Pulls power from source)
- Available in multiple lengths
- Premium Tinned Copper Braid construction
- Plug-and-play, no additional drivers required
- Plenum CL2P rated jacket for in-ceiling use
- Lifetime Warranty



Specifications

- Performance Grade: Better
- Connector Type 1: USB A male
- Connector Type 2: USB A female
- Bandwidth: Supports 480 Mbps High Speed, 12 Mbps Full Speed and 1.5 Mbps Slow Speed
- Shielding: 65% Braid
- Gauge: 24/22AWG
- Jacket: Plenum CL2P rating
- UL Rated: Yes
- RoHS Compliant: Yes
- Temperature Rating: 75° C
- Voltage: 30V
- Warranty: Lifetime

USB2-AMF-25PROAP
USB2-AMF-35PROAP
USB2-AMF-50PROAP

25ft.
35ft.
50ft.

USB2-AMF-65PROAP
USB2-AMF-75PROAP

65ft.
75ft.