



Anixter PN: RG59SIAMCCAPLN-B5CBK

Number of Conductors:	Siamese	Jacket Material:	LS PVC
Conductor:	Bare Copper	Jacket Thickness (in):	Coax:0.022 18/2C:0.020
Gauge Size:	Coax: 20AWG 2C: 18AWG Coax: Solid 2C: Stranded	Jacket Color:	Black
Conductor Stranding:	7	Rip Cord:	No
Insulation Material:	Coax: Foamed FEP 18/2C:PVC	Nominal Cable OD (in):	0.432 x 0.245
Insulation Thickness	Coax: 0.054 2C:0.008		
Insulation Color Code:	18/2C: Black Red		
Shield:	Coax: Braid 2C: None	Putup Length:	500
Shield Material:	Copper Clad Aluminum	Putup Type:	Box
Shield Coverage(%)	95	Weight(lbs/kft):	52
Standards:	CMP UL 444 NEC 800 NFPA 262 CL3P UL 13 NEC 725 NFPA 262		
Print Legend:	RG59/U 20 AWG 1/C 18 AWG 2/C (UL) TYPE CMP/CL3P SUN RES (E-File #) (Footage Marking)		
Operating Temp	-20 to +75		
Voltage Rating	300		
Capacitance(pF/ft):	Coax: 17		
Impedance(Ohms):	Coax: 75		

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.