

HID[®] Prox I25 kHz Proximity – Readers



	ProxPoint Plus [®]	MiniProx [®]	Thinline [®] II	ProxPro [®]	ProxPro [®] II	ProxPro [®] with Keypad	EntryProx [™]	MaxiProx [®]	Prox80 [™]
Base Model Number	6005B/6008B	5365E/5368E	5395C/5398C	5355A/5352A/ 5358A	5455B/ 5458B	5355A/5352A/ 5358A	4045C	5375A	5405A/5408A
Dimensions	3.13" x 1.7" x 0.66" (8.0 cm x 4.5 cm x 1.5 cm)	6.0" x 1.7" x 1.0" (15.0 cm x 4.5 cm x 2.0 cm)	4.7" x 3.0" x .68" (12.0 cm x 7.5 cm x 1.5 cm)	5.0" x 5.0" x 1.0" (12.5 cm x 12.5 cm x 2.5 cm)			5.25" x 2.75" x 1.37" (13.5 cm x 7.0 cm x 3.5 cm)	12.0" x 12.0" x 1.0" (30.5 cm x 30.5 cm x 2.5 cm)	3.15" x 3.15" x 0.8" (8.0 cm x 8.0 cm x 2.0 cm)
Weight	3.6 oz (102 g)	7.89 oz (224 g)	7.33 oz (208 g)	9.62 oz (273 g)	13.65 oz (387 g)	9.62 oz (273 g)	11.76 oz (333 g)	50.8 oz (1440 g)	2.2 oz (63 g)
Read Range	Up to 3.0" (7.5 cm)	Up to 5.5" (14.0 cm)		Up to 8.0" (20.5 cm)			Up to 3.0" (7.5 cm)	Up to 24.0" (61.0 cm)	Up to 5.5" (14.0 cm)
Mounting	Mullion		Single-gang electrical box	Single-gang electrical box; Glass Mount Kit Available			US or EU single gang box, wall surface, or on glass with included adhesive pads	Mount on non-metallic surfaces for optimal read range performance.	EU/Asian single-gang box
Power Supply	5-16 VDC			10-28.5 VDC	5-16 VDC	10-28.5 VDC	10-15 VDC	12 VDC or 24 VDC	5-16 VDC
Current Requirements	35 mA			155 mA	40 mA	155 mA	150 mA	200/700 mA @ 12 VDC 260 mA/1.2 A @ 24 VDC	35 mA
Termination	Pigtail	Pigtail or Terminal Strip	Pigtail			Terminal Strip			Pigtail
Output Formats	Wiegand or Clock-and-Data			Wiegand, Clock-and-Data, RS-232 or RS-422	Wiegand or Clock-and-Data	Wiegand, Clock-and-Data, RS-232 or RS-422	Wiegand	Wiegand, Clock-and-Data, RS-232, RS-422 and RS-485	Wiegand or Clock-and-Data
Tamper	No			Switch	No	Switch		Switch	No
Indoor/Outdoor	Both								
Warranty	Lifetime								

HID Prox