



RS-2G

Redwood® Sensor Pod, Generation 2

- Light level sensor
- Ambient temperature sensor
- Infrared motion sensor
- Connects to gateway

General Specifications

Generation	2
Product Type	Sensor Pod
Application	Collects sensor data
Brand	Redwood®
Color	White
Data Ports, quantity	1
Includes	Collar RJ25 cable
Mount Type	Ceiling
Package Quantity	1
Ordering Note	Available in Asia Pacific Available in Europe Available in the United States and Canada

Dimensions

Cable Length	2.1 m 7.0 ft
Height	45.72 mm 1.80 in
Inner Diameter	25.40 mm 1.00 in
Outer Diameter	40.64 mm 1.60 in
Weight	0.11 kg 0.25 lb

Mechanical Specifications

Gateway Connector Interface	RJ25
Material Type	Plastic

Electrical Specifications

ANSI/TIA Category	5e 6 6A
Power Consumption, maximum	10 mW

Environmental Specifications

Ambient Temperature Sensor Range	0 °C to +100 °C (+32 °F to +212 °F)
Ambient Temperature Sensor Tolerance	
Environmental Space	Indoor Plenum
Operating Humidity	10%–80%, non-condensing
Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Storage Humidity	5%–95%, non-condensing
Storage Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

RS-2G

Safety Standard AS/NZS CISPR 22 | c-UL-us | CE | CEC Title 24-2008 | IEC 60950 | IEC 61000-4.5, Class 3 | UL 60950 | UL 924 | UL-us | US FCC Part 15, Class A

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

