

10

Model : V24UK-32A

1650

3000

30

1 - 4

5 - 8

9 - 12

13 - 16

17 - 20

21 - 24

IEC 60309

32A 2P+E PLUG

32A Rating PDU, the models which have 24 socket outlets,

< CIRCUIT A > Socket #1-12 UK socket outlets can only output 16A maximum.

< CIRCUIT B > Socket #13-24 UK socket outlets can only output 16A maximum.

Cordset

:

3 meter 4mm sq H05V V-F cable with IEC60309 32A 2P + E plug

Input Rating

:

32A / 240Vac

Regulatory :

Model : V24UK-20A

20 Amp

Open end

Cordset

:

3 meter 2.5mm sq H05V V-F cable with 20 Amp open-end

Input Rating

:

20A / 240Vac

Model : V24UK-16A

IEC 60309

16A 2P+E PLUG

OR

16 Amp

IEC320 C20

Cordset

:

3 meter 1.5mm sq H05V V-F cable with IEC60309 16A 2P + E or IEC320 C20 plug

Input Rating

:

16A / 240Vac

Model : V24UK-13A

13 Amp

BS1363

Cordset

:

3 meter 1.5mm sq H05V V-F cable with 13 Amp BS1363 plug

Input Rating

:

13A / 240Vac

UNIT : mm

Common Specification :

- Description : 24 outlets UK, 45 degree (left side mounting)
- Receptacles : 24 outlets UK BS1363 13A Rated, Angled 45 degree

- PDU Dimension : 60 (W) x 50 (D) x 1650 (H) mm
- Packing :

- Net Weight :
- Gross Weight :

WARNING : The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2012 Austin Hughes Electronics Ltd. All rights reserved.