

VERTICAL MANAGER/DOOR MATRIX

NetRunner Vertical Cable Manager



- Includes hinged covers, cable retainers, mounting brackets and 12-24# screws
- Integral cable retainers on the end of each finger help contain cables within each rack
- Dual-hinged covers open 110 degrees to provide complete access
- Larger finger openings accommodate up to 24 CAT6 cables

Part	Description	RU	Height	Width	Depth
WMPV45E	Dual-sided vertical manager	45	83" (2108mm)	4.9" (125mm)	12" (306mm)
WMPVHC45E	Dual-sided vertical manager	45	83" (2108mm)	6.7" (170mm)	14.1" (357mm)
WMPVF45E	Dual-sided vertical manager	45	83" (2108mm)	4.9" (125mm)	6.5" (165mm)
WMPV22E	Dual-sided vertical manager	22	41.5" (1054mm)	4.9" (125mm)	12" (306mm)

NetRunner High-Capacity Vertical Cable Manager



- Includes cable retainers, mounting brackets and 12-24# screws
- Zero RU counting expands functionality
- Larger finger openings accommodate up to 24 CAT6 cables
- Managers accommodate up to 43% more cable fill than standard NetRunner
- Optional dual-hinged doors and end-panel (NREP B1) provide a cleaner appearance.

Part	Description	RU	Height	Width	Depth	Compatible Door
NRV6	Dual-sided vertical manager	45	80.4" (2042mm)	6.7" (170mm)	13.8" (350mm)	NRD6B1
NRV10	Dual-sided vertical manager	45	80.4" (2042mm)	10" (254mm)	13.8" (350mm)	NRD10B1
NRV12	Single-sided vertical manager	45	80.4" (2042mm)	12" (1305mm)	13.8" (350mm)	NRD12B1
NRVF6	Single-sided vertical manager	45	80.4" (2042mm)	6.7" (170mm)	7.48" (190mm)	NRD6B1
NRVF10	Single-sided vertical manager	45	80.4" (2042mm)	10" (254mm)	7.48" (190mm)	NRD10B1
NRVF12	Single-sided vertical manager	45	80.4" (2042mm)	12" (1305mm)	13.8" (350mm)	NRD12B1

PatchRunner Vertical Cable Manager



- High density minimizes area required for network layout, freeing up valuable floor space
- Curved cable management fingers support cables transition to the vertical pathway eliminating the needs for horizontal managers
- Individual fingers can be safely "snapped off" for routing of larger cable bundles.
- Fingers align with rack spaces simplifying cable routing
- Optional dual-hinged doors and end-panels provide a cleaner appearance.

Part	Description	RU	Height	Width	Depth	Compatible Door
PRV6	Dual-sided vertical manager	45	84" (2133mm)	6" (152.4mm)	16.4" (417mm)	PRD6
PRV8	Dual-sided vertical manager, includes for PRSP7 slack spools	45	84" (2133mm)	8" (203mm)	16.4" (417mm)	PRD8
PRV10	Dual-sided vertical manager, includes for PRSP7 slack spools	45	84" (2133mm)	10" (254mm)	16.4" (417mm)	PRD10
PRV12	Dual-sided vertical manager, includes for PRSP7 slack spools	45	84" (2133mm)	12" (305mm)	16.4" (417mm)	PRD12
PRV15	Dual-sided vertical manager, includes for PRSP7 slack spools	45	84" (2133mm)	15" (381mm)	16.4" (417mm)	PRD15

Available in 8' (95.5" 2426mm) = add 96 to end of part number.

Single-sided vertical managers available in all sizes listed as PRVF

PatchRunner High-Capacity Vertical Cable Manager



- High density minimizes area required for network layout, freeing up valuable floor space
- Large finger spacing accommodates up to 48 CAT6a cables
- Ventilated side walls provide maximum airflow for cooling equipment and extra tie-off points
- Individual fingers can be safely "snapped off" for routing of larger cable bundles.
- Fingers align with rack spaces simplifying cable routing
- Optional dual-hinged doors and end-panels provide a cleaner appearance.

Part	Description	RU	Height	Width	Depth	Compatible Door
PEV6	Dual-sided vertical manager	45	83.5" (2120mm)	6" (152.4mm)	28.1" (714mm)	PED6B1
PEV8	Dual-sided vertical manager	45	83.5" (2120mm)	8" (203mm)	28.1" (714mm)	PED8B1
PEV10	Dual-sided vertical manager	45	83.5" (2120mm)	10" (254mm)	28.1" (714mm)	PED10B1
PEV12	Dual-sided vertical manager	45	83.5" (2120mm)	12" (305mm)	28.1" (714mm)	PED12B1

Available in 8' (95.5" 2426mm) = add 96 to end of part number.

Single-sided vertical managers available in all sizes listed as PEVF.

Available unassembled (shipped flat pack) add B1 to the end of the part number.

Most popular products are listed above and highlighted in BOLD. Check out Panduit.com for all sizes and accessories.