
Item no.:	281-407
Product description:	TEST PLUG 6 MM / 0.236 IN WIDE NOMINAL CURRENT 24 A for 0.08 mm ² - 2.5 mm ²



Produkt kann von Bild abweichen / product may differ

Packing unit 100 4*25 pieces

RoHS compliant

Cross section to [AWG]	14 AWG
Cross section [AWG]	28 - 0.08 mm ²
Width	0.236 in
Strip length	0.33 in
Cross section to [mm ²]	2.5 mm ²
Width	6 mm
Strip length from	8 mm
Strip length to	9 mm
No. of connection Points	1
No. of potentials	1
Product group	1 (Rail Mounted Terminal Blocks)
Current intensity EN	24 A
Weight	2.163 g
Color	gray