

960H Wide Dynamic Range Indoor/Outdoor IR Bullet Camera

WDRB10H 2.8-12mm auto iris varifocal lens, dark grey housing

Features

- True WDR technology allows for improved image quality in scenes consisting of both bright and dark areas
- 1/3" Sony Super HAD™ CCD
- 700 TV lines of resolution
- 42 IR LEDs
- Highest resolution: vivid sharp picture in complete darkness
- 3DNR (digital noise reduction)
- Smart digital zoom
- Full OSD operation
- Digital image stabilizer
- 3 axis lens mount
- IP67 compliant
- 12VDC / 24VAC dual voltage operation
- 5 year warranty



Specifications

Image Sensor	1/3" Sony Super HAD™ CCD (dual scan)
Resolution	700 TV lines
Minimum Illumination	0.000006 lux @ F1.2 / IR LED On
Effective Pixels	976 (H) x 494 (V)
Total Pixels	1028 (H) x 508 (V)
TV System	NTSC
Scanning System	2:1 interlace
Number of IR LEDs	42
IR Range	98 ft. (depending on scene reflection)
IR LED Wavelength	850nm
S/N Ratio	52dB
Video Output	1.0Vp-p / 75 ohms
Backlight Compensation	BLC / HLC / Off
Day/Night	Auto / Color / BW / Ext
AGC	High / Middle / Low
Sense-Up	Auto / Off (x2 – x512)
White Balance	ATW / AWB / AWC – Set / Manual (1,800°K – 10,500°K)

Mirror	H-Rev / V-Rev / Rotate / PIP
Digital Zoom	x16
Defect Compensation	Auto (64 points)
3DNR	Off / Low / Mid. Low / Mid. High / High
DIS	On / Off
Power Supply	12VDC / 24VAC dual voltage operation (power supply not included)
Power Consumption	12VDC, 700mA / 24VAC, 350mA
Storage Temperature/	
Humidity	-4° F – 140° F / 20% – 95% RH
Operating Temperature/	
Humidity	-4° F – 140° F / 20% – 80% RH
Dimensions	3.94" (W) x 3.94" (H) x 8.27" (L)
Weight	3.09 lbs.



WDR



no WDR

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/13/14



Optional Accessories



INTCM
Corner/Pole
Adaptor



INTJBS
Square
Junction Box



CVCJBB
Round
Junction Box



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply