

Anixter Level 2 for Industrial Network Environments

Industrial Ethernet Connector: Cat 6A Stranded Shielded RJ45



L2-M-6-RJ45-SHD-STR	Cat 6A Industrial Ethernet Ruggedized Plug Kit, stranded shielded, UTP/STP IP20
----------------------------	---

Connector Specifications	
Sealing:	Suitable for IP20
Connector Interface:	IEC 60603-7
Stranding	Yes
Shielding:	Yes
Electrical Performance:	Cat 6A
Maximum Operating Voltage:	300 V RMS
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-40°C To +70°C
Applicable Standards:	ANSI/TIA/EIA-568-C.2, EtherNet/IP Specification, UL1863

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.
We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.