

Anixter Level 1 for Industrial Network Environments

Industrial Ethernet Patch Cords: Cat 5e Stranded Unshielded



Product Description	Cat 5e 300V Stranded Unshielded Cordage Modular Patch Cord, RJ45 Plug, Dark Gray Jacket, 1M, 2M, 3M and 5M lengths.
----------------------------	---------------------------------------------------------------------------------------------------------------------

Anixter Part #	Length
L1-1M-CAT5-STR	1 Meter
L1-2M-CAT5-STR	2 Meter
L1-3M-CAT5-STR	3 Meter
L1-5M-CAT5-STR	5 Meter

Electrical Specifications	
ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V
Environmental Specifications	
Environmental Space	Nonplenum
Flammability Rating	UL 94 V0
Operating Temperature	10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	Anatel cETL ETL

General Specifications	
Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	Dark gray
Mechanical Specifications	
Conductor Type	Stranded
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 30 lbf
Wiring	T568B

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
 Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.

We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations

to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.