

Anixter Level 2 for Industrial Network Environments

Industrial Ethernet Patch Cords: Cat 5e Solid Shielded



Product Description	Industrial Ethernet Patch Cords, Solid Shielded, Cat 5e 4-Pair, 24 AWG – Heavy Duty Oil- & Sunlight-Resistant Black Jackets with both sides connectorized to 8 position, IP20 industrial RJ45 crimp male connector and molded boot. 1M, 2M, 3M, AND 5M lengths
----------------------------	--

Anixter Part #	IP Rating	Length
L2-1M-CAT5-SHLD	IP20	1 Meter
L2-2M-CAT5-SHLD	IP20	2 Meter
L2-3M-CAT5-SHLD	IP20	3 Meter
L2-5M-CAT5-SHLD	IP20	5 Meter

Applicable Specifications and Agency Compliance (Overall)	
Applicable Standards & Environmental Programs	
EU Directive 2002/95/EC (RoHS):	Yes
Connectors	
Description:	RJ45 plugs. Suitable for use in IP20 applications
Connector Type:	RJ45
Sealing:	Suitable for IP20
Connector Interface:	IEC 60603-7
Shielding:	Yes
Electrical Performance:	Cat 5e
Maximum Operating Voltage:	300 V RMS (600 V AWM Rated)
Applicable Standards:	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801

Assembly	
Electrical Performance:	Cat 5e
Maximum Operating Voltage:	300 V RMS (600 V AWM Rated)
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C
Applicable Standards:	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801, UL 1863 and CSA-22.2 No. 233

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.
We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.