

Anixter Level 3 for Industrial Network Environments

Industrial Ethernet Patch Cords: Cat 5e Stranded Unshielded



Product Description	EtherNet/IP, Stranded/Unshielded high-flex, double-ended patch cord, M12 male to male straight, 4-pin, D-coding, 24 AWG TPE cable, oil resistance, 2-Pair with teal jacket.
----------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Anixter Part #	IP Rating	Length
L3-2M-CAT5-STR	IP68	2 Meter
L3-5M-CAT5-STR	IP68	5 Meter
L3-10M-CAT5-STR	IP67	10 Meter

Ethernet/IP Double-Ended Patch Cord: CAT 5e, High-Flex, 2 Pair, Stranded/Unshielded, 24 AWG, TPE Jacket	
Degree of protection	IP68
Temperature	-40°C to 75°C
Mechanical	
M12 and M12 Receptacle	
Molded body	PUR, black
Coupling nut	Metal
Contacts	Gold/silver plated
Insert	PUR, black
Electrical	
Current rating	4A
Voltage rating	250V
Performance	CAT5e

Cable Specifications	
Cable jacket	TPE
Color	Teal
Overall diameter	0.275 in.
Conductor	Stranded copper
Temperature	Operating: -40°C to 75°C / Installation: -25°C to 75°C
Flame test	UL: CMR / CSA: CMG

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.

We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations

to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW,
ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED,
ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.