DS915 Recess Mount PIR Detector

www.boschsecurity.com





- ▶ Pulse count of one, two, or three
- ► Five field-changeable Fresnel lenses
- ► Semi-flush in standard switch box
- ▶ Ideal for new construction
- ▶ Internal vertical and horizontal pointability

The DS915 PIR Detector is designed to mount in a standard single gang electrical box or directly to a wall using the supplied flush mount ring. It uses alternate polarity pulse count processing, is internally pointable and uses grooves-in Fresnel lenses to provide six different coverage patterns.

Functions

Signal Processing

Alternate polarity pulse count. Field-selectable for one, two, or three pulses.


Test Features

External visible alarm LED. Internal noise voltage output provides precise pattern location and background disturbance evaluation using a standard analog meter.


Certifications and approvals

Region	Certifi	cation
USA	UL	ANSR: Intrusion Detection Units (UL639)

Installation/configuration notes



Top View Standard Broad Coverage: 10 m x 12 m (30 ft x 38 ft)




Side View Standard Broad Coverage: 10 m x 12 m (30 ft x 38 ft)



Top View Optional Barrier Coverage (OLB91): 10 m x 1.5 m (30 ft x 4.8 ft)



Side View Optional Barrier Coverage (OLB91): 10 m \times 1.5 m (30 ft \times 4.8 ft)




Top View

Optional Pet Coverage (OLP91): 10 m \times 12 m (30 ft \times 38 ft)




Side View Optional Pet Coverage (OLP91): 10 m x 12 m (30 ft x 38 ft)



Top View Optional Dense Wide Angle Coverage (OLW91): 10 m x 15 m (30 ft x 50 ft)



Side View Optional Dense Wide Angle Coverage (OLW91): 10 m \times 15 m (30 ft \times 50 ft)



Top View Optional Dual Corridor Coverage (OLC91): 18 m (60 ft) with 10 m x 10 m (30 ft x 30 ft) center



Side View

Optional Dual Corridor Coverage (OLC91): 18 m (60 ft) with 10 m x 10 m (30 ft x 30 ft) center

Technical specifications

Enclosure Design

Dimensions:	12.5 cm x 8.4 cm x 2.0 cm (4.875 in. x 3.25 in. x 0.625 in.)
Material:	High impact ABS plastic enclosure

Environmental Considerations

Operating	-29°C to +49°C (-20°F to +120°F)
Temperature:	For UL Certificated installations, 0°C to +49°C (+32°F to +120°F)
Radio Frequency Interference (RFI) Immunity:	No alarm or setup on critical frequencies in the range from 26 MHz to 950 MHz at 50 V/m.

Mounting

Height Range:	2m to $2.6m$ (6.5 ft to 8.5 ft) recommended
Pattern Pointability:	Coverage is adjustable $+2^{\circ}$ to -14° vertically, $\pm 10^{\circ}$ horizontally.

Power Requirements

Current Draw:	20 mA at 12 VDC
Voltage:	10 VDC to 15 VDC
Alarm Output:	Normally-closed reed relay rated at 3.0 W, 125 mA at 28 VDC for resistive loads and protected by a 4.7 Ω resistor in the common C leg.

Ordering information

DS915 Recess Mount PIR Detector

Provides pulse count processing, movable lenses, and six coverage patterns.

Order number **DS915**

Accessories

OLB91-3 Barrier Lens Kit

Provides barrier coverage with a 10 m x 1.5 m (30 ft x 4.8 ft) pattern. Shipped in packages of three. Order number **OLB91-3**

OLC91-3 Dual-corridor Lens Kit

Provides coverage for two corridors with two 18 m (60 ft) barriers and a 10 m x 10 m (30 ft x 30 ft) central coverage pattern. Shipped in packages of three.

Order number OLC91-3

OLP91-3 Pet Lens Kit

Provides pet-avoidance coverage with a $10 \text{ m} \times 12 \text{ m}$ (30 ft x 38 ft) pattern. Shipped in packages of three. Order number **OLP91-3**

OLW91-3 Dense Wide-angle Lens Kit

Provides dense wide-angle coverage with a 10 m \times 15 m (30 ft \times 50 ft) pattern. Shipped in packages of three.

Order number OLW91-3

TC6000 Test Cord

Test cord for connecting a compatible detector's test pins to a voltmeter. It is 4.6 m (15 ft) long.

Order number **TC6000**

Represented by:

Americas:

Americas:
Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180 security.sales@us.bosch.com www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V. P.O. Box 80002 P.O. Box 80002 5617 BA Eindhoven, The Netherlands Phone: + 31 40 2577 284 Fax: +31 40 2577 330 emea.securitysystems@bosch.com www.boschsecurity.com

Asia-Pacific:

Asia-Pacific:
Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

China:
Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398 www.boschsecurity.com.cn

America Latina:

America Latina:
Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com