


D7044M Multiplex Mini Single-input Module

www.boschsecurity.com



BOSCH
Invented for life



- ▶ Use with D7024, DS9400M, or FPD-7024 Addressable FACP's
- ▶ Fits into a standard single-gang back box
- ▶ Easy addressing using rotary switches
- ▶ Low current draw
- ▶ UL Listed

The D7044M Multiplex Mini Single-input Module connects a normally-open (NO) contact to the multiplex bus of a D7024, DS9400M or FPD-7024 Addressable Fire Alarm Control Panel (FACP). Use the module's supervised input in a Class B configuration. All operating power for the input module is drawn from the FACP. Rotary switches allow convenient address setting.



Notice

The D7024 is **not** listed under UL864, 9th edition.

Certifications and approvals

Region	Certification	
USA	UL	UQJZ: Control Units, System (ANSI/UL 864) and UOXX: Control Unit Accessories, System (ANSI/UL 864)
	FM	D7044\D7044M
	CSFM	see our website
	FDNY-CoA	#6173

Installation/configuration notes

Compatible Products

The following products are compatible with the D7044 Multiplex Single-input Module:

Category	Product ID	Product Description
Control Panels	D7024	Addressable FACP
	D7024-EXP	Addressable FACP for export
	DS9400M	Addressable FACP
	FPD-7024	Addressable FACP
Modules	D7039	Multiplex expansion module

Mounting

The module fits in a single-gang back box to which the device it is monitoring is attached.

Wiring

Connections for the module are made using the 16 AWG (ISO 1.5 mm²) flying leads from the device. All wiring is power limited and supervised.



Notice

Do not use shielded wire.

**Notice**

Supervise the input loop with the supplied EOL resistor.

Parts included

Quant.	Component
1	D7044M module
1	2.21 kΩ end-of-line (EOL) resistor (P/N: 25899)
1	Literature pack

Technical specifications**Circuit Designation**

MUX Bus:	Supervised Class A (Style 6) SLC or Class B (Style 4) SLC
Input:	Supervised Class B (Style B) IDC

Environmental Considerations

Environment:	Indoor, dry
Relative Humidity:	Up to 93% non-condensing
Temperature (operating):	+32°F to +120°F (0°C to +49°C)

Input

Type:	One normally-open (NO) contact input supervised by a 2.21 kΩ EOL resistor (P/N: 25899).
-------	---

Mechanical Properties

Color:	White
Dimensions (HxWxD):	1.5625 in. x 2.75 in. x 0.6875 in. (4 cm x 7 cm x 1.75 cm)
Material:	ABS plastic
Weight:	2.9 oz (82 g)

Power Requirements (supplied from FACP's MUX bus)

Current:	0.55 mA
Voltage (minimum):	8 V peak (12 VDC nominal)

Ordering information**D7044M Multiplex Mini Single-input Module**

Connects a normally-open (NO) contact to the multiplex bus of a D7024, DS9400M or FPD-7024 Addressable FACP

Order number **D7044M**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com