

FMM-100SAT2CKEX Explosion-proof Fire Alarm Manual Station

www.boschsecurity.com



- ▶ Special hazard protection; NEMA 4X and marine ratings
- ▶ Gold-plated alarm contacts for corrosion resistance
- ▶ Key lock reset with optional break rod
- ▶ ADA compliant; UL Listed, FM Approved

The FMM-100SAT2CKEX is a high-quality, die-cast metal fire alarm manual station that is UL and FM Listed for use in Class I, Division I, Groups B, C, and D; Class II, Division I, Groups E, F, and G; and Class III (FM Listed only) hazardous locations. It is also marine and NEMA 4X rated for use in harsh environments. It complies with Americans with Disabilities Act (ADA) requirements and meets ADA standards for wheelchair access when properly installed.

Functions

Operation
When the bar on the front of the manual station is pulled, it latches open and is easily visible from 50 ft (15 m). Reset the activation bar by opening the manual station with the key and placing the activation bar in its normal upright position. An optional scored acrylic break rod is provided.

Certifications and approvals

Signal Communications Corp. holds these listings and approvals:

NYC/MEA	382-94-E, Vol. 5
NEMA	Complies with National Equipment Manufacturers Association NEMA 4X
ADA	Complies with Americans with Disabilities Act

Region	Certification	
USA	UL	UCCM: Boxes, Non-Coded, Marine and UHMV: Fire Alarm Devices for Use in Hazardous Locations (ANSI/NFPA 70, "National Electrical Code" (NEC), or United States Coast Guard (USCG) Electrical Engineering Regulations 46CFR110, "General Provisions," 46CFR111, "Electric Systems - General Requirements," 46CFR112, "Emergency Lighting and Power Systems," and 46CFR113, "Communication and Alarm Systems and Equipment")
	FM	FMM-100SAT2CKEX
	CSFM	see our website

Installation/configuration notes

Compatibility Information

The explosion-proof manual station is compatible with all Bosch Security Systems, Inc. Fire Alarm Control Panels.

Mounting Considerations

The explosion-proof manual station must be surface mounted on a flat wall. It has two conduit entries. Any conduit entry that is not used must be plugged. To comply with ADA standards, the manual station must be less than 48 in. (1.2 m) above the floor for front wheelchair access and less than 54 in. (1.3 m) above the floor for side wheelchair access.

Parts included

Quant.	Component
1	Manual station with back box
1	D102 Key (1358 key)
1	Scored acrylic break rod
1	Hardware pack
1	Literature pack

Technical specifications

Environmental

Protection Category:	IP66
Relative Humidity:	90% at +100°F (+38°C)
Temperature (operating):	-40°F to +150°F (-40°C to +66°C)

Mechanical

Color:	Red
Dimensions (H x W x D):	6.3125 in. x 3.25 in. x 3.875 in. (16 cm x 8.3 cm x 9.8 cm)
Material:	Die-cast metal
Weight:	4.8 lb (2.2 kg)

Outputs

Alarm Contacts:	Two Form C contacts; each contain one normally-open (NO), one normally-closed (NC), and one common. Either the NO or the NC with the common can be wired to the terminal block. All contacts rated for 1 A at 30 VDC or 120 VAC
-----------------	---

Ordering information

FMM-100SAT2CKEX Explosion-proof Fire Alarm Manual Station

High-quality, metal manual fire station in red
Order number **FMM-100SAT2CKEX**

Accessories

D102 Replacement Key

Replacement key (#1358) for LOCK-1358 and the D101 lock.

Order number **D102**

FMM-100GR Scored Acrylic Break Rods

Scored acrylic rods (12 per package)

Order number **FMM-100GR**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com