D284 Ultraviolet Flame Detector

www.boschsecurity.com





- ► Highly reliable, long-lasting ultraviolet (UV) receptor tube
- ▶ Low power consumption
- ► Can be mixed with other detector types on the control panel's initiation detection circuit (IDC)
- Easily maintained; can be cleaned without disassembly

Use the D284 wherever fires can develop quickly. Suitable applications are:

- · Petroleum storage areas
- · Photographic or film storage areas
- Computer rooms
- Print shops
- Museums



Notice

The D284 is not a substitute for smoke or heat detectors. It provides an added level of notification for fast flaming fires only.



Notice

This product is not UL Listed.

Functions

Basic Operation

An ultraviolet-detector tube within the D284 absorbs very weak ultraviolet (UV) light such as that emitted from a flame and produces an electrical current. The detector's electronic circuitry translates this current into an alarm signal. A counter-current prevents alarm

signals from single-pulse UV sources such as lightning or cosmic flares. Additionally, the circuit is tuned to respond only to wavelengths from 185 nm to 300 nm.

Coverage Area

The D284's response depends on both the size of the fire and the distance from the fire to the detector; therefore the effective coverage area varies. Very small fires must have a duration of at least 7 sec if within 12 ft (3.7 m) of the detector and a duration of 30 sec if within 12 ft to 25 ft (3.7 m to 7.6 m) of the detector.

Installation/configuration notes

Compatibility Information

The D284 is compatible with the following products:

Category	Product ID	Product Description
Control Panels:	All Bosch Security Systems 24 V fire alarm control panels	
Detector Bases:	D250A ¹	Two-wire detector base (12/24 VDC)
	D253	Two-wire detector base (24 VDC)
	D261AW ¹	Two-wire detector base (12/24 VDC)
	D261W1	Two-wire detector base (12/24 VDC)

2 | D284 Ultraviolet Flame Detector

D271W1 Four-wire detector base (12/24 VDC) D280A Two-wire detector base (24 VDC) D290 Four-wire detector base (24 VDC)

¹ All 12 VDC or 24 VDC bases must be set for 24 VDC operation.

Parts included

Quant.	Component
1	Flame detector

Technical specifications

Environmental Considerations

Relative Humidity:	up to 95%, non-condensing at +104°F (+40°C)
Temperature (operating):	+14°F to +122°F (-10°C to +50°C)

Mechanical Properties

Color:	lvory
Dimensions (diameter x H)	4 in. x 2 in. (10.2 cm x 5.1 cm)
Material:	ACS plastic (acrylonitrile-chlorinated PE-styrene)

Output

Contact Rating:	260 mA at 24 VDC
-----------------	------------------

Power Requirements

Voltage (operating)	
Standby:	0.2 mA at 24 VDC
Alarm:	0.25 mA at 24 VDC
Current	

Nominal:	24 VDC
Range:	17.6 VDC to 27.7 VDC

Response

Detection Angle:	120° conical
UV Sensitivity:	185 nm to 300 nm

Ordering information

D284 Ultraviolet Flame Detector

The D284 is an ultraviolet light lame detector that provides an added level of notification for fast flaming fires only. It is not a substitute for smoke or heat detectors and is not UL Listed. Order number **D284**

Accessories

D250A Two-wire Detector Base (12/24 VDC)

Accepts Bosch D254 and D255 heat detector heads Order number D250A

D253 Two-wire Detector Base (24 VDC)

A two-wire 24 VDC heat detector base, with a latching steady-on alarm LED, that accepts Bosch D254 and D255 heat detector heads Order number **D253**

D261AW Two-wire Detector Base (12 VDC or 24 VDC)

12 VDC or 24 VDC, two-wire circuit compatibility Order number **D261AW**

D261W Two-wire Detector Base (12/24 V)

A white, 6 in. (15.24 cm) diameter, two-wire detector base that operates at 12 VDC or 24 VDC. Order number **D261W**

D280A Two-wire Detector Base (24 VDC)

24 VDC, two-wire photoelectric smoke detector Order number D280A

D290 Four-wire Detector Base (24 VDC)

24 VDC, four wire circuit compatibility Order number D290

Represented by:

Americas:

Americas:
Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180 security.sales@us.bosch.com www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V. P.O. Box 80002 P.O. Box 80002 5617 BA Eindhoven, The Netherlands Phone: + 31 40 2577 284 Fax: +31 40 2577 330 emea.securitysystems@bosch.com www.boschsecurity.com

Asia-Pacific:

Asia-Pacific:
Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

China:
Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398 www.boschsecurity.com.cn

America Latina:

America Latina:
Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com