

DS422i and DS426i Dual-Beam Photoelectric Detectors

www.boschsecurity.com



BOSCH

Invented for life



- ▶ Dual beam detection
- ▶ Range up to 60 m (200 ft) outdoors, 180 m (600 ft) indoors
- ▶ Selectable response time
- ▶ Small unobtrusive design

The DS422i and DS426i are dual-beam photoelectric detectors designed for indoor and outdoor applications. Consisting of a separate transmitter and receiver, they are designed to activate an alarm when an intruder passes within the direct line of sight between the transmitter and receiver.

The DS422i has a range of 30 m (100 ft) outdoors or 90 m (300 ft) indoors. The DS426i has a range of 60 m (200 ft) outdoors or 180 m (600 ft) indoors.

Certifications and approvals

Region	Certification	
Europe	CE	
USA	UL	ANSR: Intrusion Detection Units (UL639)
China	CCC	2009031901000200

Installation/configuration notes

Mounting Considerations

Can be surface or pole mounted.

Technical specifications

Photobeam

DS422i Range	Indoor: 90 m (300 ft), Outdoor: 30 m (100 ft)
DS426i Range	Indoor: 180 m (600 ft), Outdoor: 60 m (200 ft)
Response Time:	Selectable from 50 ms to 700 ms

Enclosure Design

Dimensions:	17.1 cm x 8.2 cm x 8.7 cm (6.75 in. x 3.25 in. x 3.5 in.)
Material:	Smoked Lexan®

Environmental Considerations

Temperature (Operating):	-25°C to 55°C (-13°F to 130°F)
--------------------------	--------------------------------

Mounting Considerations

Pointability:	Adjustable ±90° horizontally, ±24° vertically
---------------	---

Outputs

Relay:	Alarm activated Form C with dry contacts rated at 0.5 A maximum at 30 VAC/VDC
Tamper:	Normally-closed with cover in place

Power Requirements

DS422i Receiver Current Draw:	31 mA
DS426i Receiver Current Draw:	31 mA
DS422i Transmitter Current Draw:	10 mA
DS426i Transmitter Current Draw:	27 mA
Voltage (Input):	12 VDC to 28 VDC, non-polarized

Trademarks

Lexan® is either a trademark or registered trademark of General Electric Company in the United States and other countries.

Ordering information

DS422i Photoelectric Detector

Provides an indoor range 90 m (300 ft), and an outdoor range of 30 m (100 ft).

Order number **DS422i**

DS426i Photoelectric Detector

Provides an indoor range of 180 m (600 ft), and an outdoor range of 60 m (200 ft).

Order number **DS426i**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: +31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com