



TECHNICAL SPECIFICATIONS		
MULTIMODE MAXIMUM LOSS	BEND RADIUS	
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	INSTALLATION	LONG TERM
	50 mm (1.97 in)	100 mm (3.94 in)
SINGLEMODE MAXIMUM LOSS	TENSILE LOAD - LSZH RATED	
.75 dB/KM @ 1310nm .75 dB/KM @ 1500nm	INSTALLATION	LONG TERM
	560 N (126 lbf)	280 N (63 lbf)
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-20°C TO +70°C -4°F TO +158°F	-20°C TO +70°C -4°F TO +158°F	-40°C TO +75°C -40°F TO +167°F

+