

| PANDUIT<br>PART NUMBER | STUD<br>SIZE | DIMENSIONS in. |               |               |                |               |
|------------------------|--------------|----------------|---------------|---------------|----------------|---------------|
|                        |              | A $\pm .03$    | W $\pm .01$   | C $\pm .02$   | M $\pm .03$    | H $\pm .01$   |
| P10-6F                 | #6           | .75<br>(19.05) | .31<br>(7.87) | .22<br>(5.59) | .55<br>(13.97) | .15<br>(3.81) |
| P10-8F                 | #8           | .78<br>(19.81) | .37<br>(9.40) | .22<br>(5.59) | .55<br>(13.97) | .17<br>(4.32) |
| P10-10F                | #10          | .78<br>(19.81) | .37<br>(9.40) | .23<br>(5.84) | .55<br>(13.97) | .20<br>(5.08) |
| P10-14F                | 1/4"         | .89<br>(22.61) | .50<br>(12.7) | .30<br>(7.62) | .60<br>(15.24) | .27<br>(6.86) |

## NOTES:


- UL LISTED AND CSA CERTIFIED FOR:
  - #12-10 AWG SOLID OR STRANDED COPPER WIRE
  - 302° F (150° C) MAX. TEMP. RATING
- MATERIAL:
  - STAMPING - .04" (1.02) THK COPPER, TIN PLATED
- SEE [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS:
  - UL LISTED AND CSA CERTIFIED: CT-100, CT-100A, CT-200, CT-570, CT-600-A, CT-1570, CT-1701, CT-2500
  - PANDUIT APPROVED: CT-160, CT-260
- WIRE STRIP LENGTH:  $9/32^{+1/32}_{-0}$  (7.1  $^{+.8}_{-0}$ )



LISTED  
587H  
E52164



CERTIFIED  
LR31212



|     |      |      |                                            |  |  |                                  |             |
|-----|------|------|--------------------------------------------|--|--|----------------------------------|-------------|
|     |      |      |                                            |  |  | <br>TINLEY PARK, ILLINOIS        |             |
|     |      |      |                                            |  |  |                                  |             |
|     |      |      |                                            |  |  |                                  |             |
| 07  | 8/11 | SHOR | MODIFIED NOTE #3, ADDED INSTALLATION TOOLS |  |  | #12-10 BARREL NON-INSULATED FORK |             |
| REV | DATE | BY   | DESCRIPTION                                |  |  | CUST                             | PM          |
|     |      |      |                                            |  |  | DRAWN BY                         | CHK'D       |
|     |      |      |                                            |  |  | DAW                              | CJH         |
|     |      |      |                                            |  |  | SCALE                            | DRAWING NO. |
|     |      |      |                                            |  |  |                                  | A41256      |