

| PANDUIT<br>PART NUMBER | WIRE<br>SIZE | DIMENSIONS in. |              |                |
|------------------------|--------------|----------------|--------------|----------------|
| PREFIX                 | AWG          | $\pm .02$      | $\pm .01$    | $\pm .01$      |
|                        |              | A              | B DIA.       | C              |
| BS18                   | 22-18        | .62<br>(15.7)  | .14<br>(3.6) | .032<br>(0.81) |
| BS14                   | 16-14        | .62<br>(15.7)  | .16<br>(4.1) | .032<br>(0.81) |
| BS10                   | 12-10        | .63<br>(16.0)  | .22<br>(5.6) | .040<br>(1.02) |

## NOTES:



- UL LISTED AND CSA CERTIFIED FOR:
  - SOLID OR STRANDED COPPER WIRE
  - 302° F (150° C) MAX. TEMP. RATING
- MATERIAL:
  - STAMPING - COPPER, TIN PLATED
- See [www.panduit.com](http://www.panduit.com) FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- INSTALLATION TOOLS:
  - UL LISTED AND CSA CERTIFIED:  
CT-100, CT-100A, CT-200, CT-570, CT-600A,  
CT-1570, CT-1701, CT-2500
  - PANDUIT APPROVED: CT-160, CT-260
- WIRE STRIP LENGTH:  $9/32^{+1/32}_{-0}$  (7.1  $^{+.8}_{-.0}$ )



LISTED  
587H  
E52164



CERTIFIED  
LR31212



**PANDUIT** CORP.

TINLEY PARK, ILLINOIS

NON-INSULATED BUTT SPLICE

DRAWN BY  
DAW

CHK'D

SCALE  
NONE

DRAWING NO.  
A41338

| 07  | 8-11 | SHOR |     | MODIFIED NOTE #3                                       |
|-----|------|------|-----|--------------------------------------------------------|
| 06  | 4-11 | SB   |     | ADDED CT-2500, CT-600A, CT1701 TOOLS.<br>ADDED NOTE #3 |
| REV | DATE | BY   | CHK | DESCRIPTION                                            |