


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #		STUD SIZE	DIMENSIONS mm				
			A ±0,51	W ±0,25	C ±0,38	M ±0,51	H ±0,25
PREF I X	PK						
PM1 - 3F	-C -M	M3	16,00 (.63)	5,84 (.23)	5,59 (.22)	12,45 (.49)	3,30 (.13)
PM1 - 4F	-C -M	M4	17,53 (.69)	8,13 (.32)	6,35 (.25)	13,46 (.53)	4,32 (.17)
PM1 - 5F	-C -M	M5	18,03 (.71)	8,80 (.35)	6,60 (.26)	13,97 (.55)	5,08 (.20)
PM1 - 6F	-C -M	M6	22,35 (.88)	11,18 (.44)	8,89 (.35)	16,00 (.63)	6,60 (.26)

NOTES:

1. USED FOR:
A. 0,5-1,5mm² (#22-18 AWG), SOLID
OR STRANDED, COPPER WIRE
2. MATERIAL:
A. STAMPING - 0,81mm (.03) THK COPPER, TIN PLATED
3. DIMENSIONS IN BRACKETS ARE IN INCHES
4. PACKAGE QTY:
A. STD: C=100
B. BULK: M=1000
5. WIRE STRIP LENGTH: 7,1 ⁺⁸₋₀ (9/32 ^{+1/32}₋₀)
6. INSTALLATION TOOLS: REF. DWGS.
A41522, A41523, A41524, A41525



A41427_02

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
02	10/97	TM		CHANGED DECIMAL POINTS TO COMMAS				NON-INSULATED METRIC FORK 0,5-1,5mm ² BARREL			
01	1/97	TM	RLS	UPDATED DIMENSIONS FILESPEC WAS NPC_A41427_00	05478	LA	DH				
00	10/91	BK	RLS	RELEASED	00687	LA	KRS				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY BDK	CHK'D	SCALE NONE	DRAWING NO. A41427