


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MARKE R PER CARDS	STYL E	LEGEND	STD. PKG. QTY.	PART NUMBER	MARKE R PER CARDS	STYL E	LEGEND	STD. PKG. QTY.
PCV-110AY	1	A	110 VOLTS	5	PCV-110BY	4	B	110 Volts	5
PCV-115AY	1	A	115 VOLTS	5	PCV-115BY	4	B	115 Volts	5
PCV-120/208AY	1	A	120/208 VOLTS	5	PCV-120/208BY	4	B	120/208 Volts	5
PCV-120AY	1	A	120 VOLTS	5	PCV-120BY	4	B	120 VOLTS	5
PCV-12470AY	1	A	12470 VOLTS	5	PCV-12470BY	4	B	12470 VOLTS	5
PCV-13200AY	1	A	13200 VOLTS	5	PCV-13200BY	4	B	13200 VOLTS	5
PCV-13800AY	1	A	13800 VOLTS	5	PCV-13800BY	4	B	13800 VOLTS	5
PCV-1PHAY	1	A	Single Phase	5	PCV-1PHBY	4	B	Single Phase	5
PCV-208AY	1	A	208 VOLTS	5	PCV-208BY	4	B	208 VOLTS	5
PCV-220AY	1	A	220 VOLTS	5	PCV-220BY	4	B	220 VOLTS	5
PCV-2300AY	1	A	2300 VOLTS	5	PCV-2300BY	4	B	2300 VOLTS	5
PCV-230AY	1	A	230 VOLTS	5	PCV-230BY	4	B	230 VOLTS	5
PCV-2400AY	1	A	2400 VOLTS	5	PCV-2400BY	4	B	2400 VOLTS	5
PCV-240AY	1	A	240 VOLTS	5	PCV-240BY	4	B	240 VOLTS	5
PCV-277/480AY	1	A	277/480 VOLTS	5	PCV-277/480BY	4	B	277/480 VOLTS	5
PCV-277AY	1	A	277 VOLTS	5	PCV-277BY	4	B	277 VOLTS	5
PCV-380AY	1	A	380 VOLTS	5	PCV-380BY	4	B	380 VOLTS	5
PCV-3PHAY	1	A	Three Phase	5	PCV-3PHBY	4	B	Three Phase	5
PCV-415AY	1	A	415 VOLTS	5	PCV-415BY	4	B	415 VOLTS	5
PCV-4160AY	1	A	4160 VOLTS	5	PCV-4160BY	4	B	4160 VOLTS	5
PCV-440AY	1	A	440 VOLTS	5	PCV-440BY	4	B	440 VOLTS	5
PCV-460AY	1	A	460 VOLTS	5	PCV-460BY	4	B	460 VOLTS	5
PCV-480AY	1	A	480 VOLTS	5	PCV-480BY	4	B	480 VOLTS	5
PCV-600AY	1	A	600 VOLTS	5	PCV-600BY	4	B	600 VOLTS	5
PCV-BLANKAY	1	A	Blank- No Legend	5	PCV-BLANKBY	4	B	Blank- No Legend	5
PCV-ESAY	1	A	Emergency Service	5	PCV-ESBY	4	B	Emergency Service	5
PCV-FAAY	1	A	Fire Alarm	5	PCV-FABY	4	B	Fire Alarm	5
PCV-FOAY	1	A	Fiber Optic	5	PCV-FOBY	4	B	Fiber Optic	5
PCV-FOCAY	1	A	Fiber Optic Cable	5	PCV-FOCBY	4	B	Fiber Optic Cable	5
PCV-MAINAY	1	A	Main	5	PCV-MAINBY	4	B	Main	5
PCV-TELEAY	1	A	Telephone	5	PCV-TELEBY	4	B	Telephone	5
					PCV-24VDCBY	4	B	24 VOLT DC	5

2



NOTE:

1. CARDS TO BE PACKAGED 5 CARDS PER BAG.
2. MILLIMETER ARE IN [].
3. SEE CUSTOMER DRAWING C10829 FOR 1/2" PCV MARKERS.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	7/25/11	RVU		ADD PCV-24VDCBY TO THE TABLE FOR 24V DC SOLAR VOLTAGE MARKER.	6470	R		
1	3/25/10	RVU		COMBINE ALL P/N WITH CUSTOMER DRAWINGS: C10358, AND C10359.	5996	R		
0	8-1-05	RVU		DRAWING RELEASE.	4101	R		

CAD FILENAME/LAYERS 100318JS-DC-C10360/03C

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
PCV'S VOLTAGE AND FIBER OPTIC MARKERS

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (.XXX) ± .025
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU MAT'L: LEGEND BLACK/ORANGE BACKGRD VINYL FILM GMVI

DATE 8-1-05

SCALE NTS

DRAWING NO. C10360 DWG A SIZE

CHK'D *[Signature]*