


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	PART DESCRIPTION	LABEL "A"	MATERIAL	ROLL LENGTH
T019X000FJC-BK	BLACK ON WHITE, POLYOLEFIN TAPE	0.19 [4.83]	GMPO	300"
T024X000FJC-BK	BLACK ON WHITE, POLYOLEFIN TAPE	0.24 [6.10]	GMPO	300"
T031X000FJC-BK	BLACK ON WHITE, POLYOLEFIN TAPE	0.31 [7.87]	GMPO	300"
T038X000FJC-BK	BLACK ON WHITE, POLYOLEFIN TAPE	0.38 [9.65]	GMPO	300"
T038X000VPC-BK	BLACK ON WHITE, VINYL TAPE	0.38 [9.65]	GMV15	300"
T038X000VYC-WH	WHITE ON BLACK, VINYL TAPE	0.38 [9.65]	GMV15	300"
T038X000YKC-BK	BLACK ON CLEAR, POLYESTER TAPE.	0.38 [9.65]	GMV4-C	300"
T050X000VPC-BK	BLACK ON WHITE, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VPC-RD	RED ON WHITE, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VQC-BK	BLACK ON BLUE, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VQC-WH	WHITE ON BLUE, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VSC-BK	BLACK ON GREEN, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VSC-WH	WHITE ON GREEN, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VUC-BK	BLACK ON ORANGE, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VWC-BK	BLACK ON RED, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VWC-WH	WHITE ON RED, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VXC-BK	BLACK ON YELLOW, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000VYC-WH	WHITE ON BLACK, VINYL TAPE	0.50 [12.70]	GMV15	300"
T050X000YKC-BK	BLACK ON CLEAR, POLYESTER TAPE.	0.50 [12.70]	GMV4-C	300"
T050X000YKC-WH	WHITE ON CLEAR, POLYESTER TAPE	0.50 [12.70]	GMV4-C	300"
T075X000VPC-BK	BLACK ON WHITE, VINYL TAPE	0.75 [19.05]	GMV15	300"
T075X000YKC-BK	BLACK ON CLEAR, POLYESTER TAPE.	0.75 [19.05]	GMV4-C	300"
T100X000VPC-BK	BLACK ON WHITE, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VPC-RD	RED ON WHITE, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VQC-BK	BLACK ON BLUE, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VQC-WH	WHITE ON BLUE, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VSC-BK	BLACK ON GREEN, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VSC-WH	WHITE ON GREEN, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VUC-BK	BLACK ON ORANGE, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VUC-WH	WHITE ON ORANGE, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VWC-BK	BLACK ON RED, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VWC-WH	WHITE ON RED, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VXC-BK	BLACK ON YELLOW, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VXC-WH	WHITE ON YELLOW, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000VYC-WH	WHITE ON BLACK, VINYL TAPE	1.00 [25.40]	GMV15	300"
T100X000YKC-BK	BLACK ON CLEAR, POLYESTER TAPE.	1.00 [25.40]	GMV4-C	300"
T100X000YKC-WH	WHITE ON CLEAR, POLYESTER TAPE	1.00 [25.40]	GMV4-C	300"



NOTES:
1. DIMENSIONS IN [] ARE IN MILLIMETERS.

CAD FILENAME/LAYERS
I00743B0_DC_C10695/16B

PANDUIT CORP. TINLEY PARK, ILLINOIS
CUSTOMER DRAWING
P1 T***X*** CASSETTE
CONTINUOUS TAPE LABEL

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1 (XXX) ± .025
(.XX) ± .030 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
I	4/14/09	LDG		ADDED T050X000VPC-RD, T100X000VPC-RD	5702	R		
O	4/30/08	RVU		DRAWING RELEASE	5403	R		

DRAWN BY
RVU
DATE
4/30/08
CHK'D

MAT'L:
SEE TABLE

SCALE
NTS
DRAWING NO.
C10695
DWG
A
SIZE