




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

2

PART NUMBER	PRINT ON AREA COLOR	APPLICATION DIAMETER RANGE	MATERIAL	"A" +/- .062 LENGTH	"B" +/- .062 PRINT ON AREA	"D" +/- .062 LENGTH	LABELS/ CASSETTE
R100X075VIC	WHITE	.120" - .160"	GMH6	.75 (19.1)	.25 (6.4)	1.25 (31.8)	150
R100X125VIC		.160" - .220"		1.25 (31.8)	.38 (9.5)	1.75 (44.5)	100
R100X150VIC		.220" - .280"		1.50 (38.1)	.50 (12.7)	2.00 (50.8)	
R100X150V2C	BLUE						
R100X150V3C	GREEN						
R100X150V7C	RED						
R100X150V8C	YELLOW						
R100X225VIC	WHITE	.280" - .390"		2.25 (57.2)	.75 (19.1)	2.75 (69.9)	75
R100X225V2C	BLUE						
R100X225V3C	GREEN						
R100X225V7C	RED						
R100X225V8C	YELLOW						

NOTES:

1. DIMENSION IN [] ARE IN MILLIMETERS.
2. SEE B20393 FOR INSTALLATION INSTRUCTIONS.



CAD FILENAME/LAYERS

100693GQ-DC-C10783/09C

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
TURN TELL ROTATABLE SELF-LAMINATING LABEL
PI CASSETTE, R***X***V*C

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (.XXX) ± .025
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

2	9/28/11	RVU		ADD NEW PN: R100X150V*C AND R100X225V*C. ADD PRINT ON AREA COLOR COLUMN.	6527	R			
1	9/24/09	RVU		DRAWING RELEASE.	5845	R			
0	9/10/09	RVU		VOID					
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	

DRAWN BY
RVU
DATE
09/1/09
CHK'D

MAT'L:
SEE TABLE

SCALE
NTS
DRAWING NO.
C10783
DWG
A
SIZE