



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CMF**	.17 LB/10 PCS (78 g/10 PCS)

- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - DIMENSIONS IN PARENTHESES ARE IN METRIC.



MODEL FILENAME	M01557AA_MC_F_ASSY_00.PRT	SIZE	A
DRAWING FILENAME	M01557AA_DC_00A.PRT		

MINI-COM™ F-TYPE COUPLER
MODULE CUSTOMER DRAWING



THIRD ANGLE
PROJECTION

PANDUIT®
CORP.
TINLEY PARK, IL 60477

ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 (,.XXX) ±.005
(.XX) ±.01 ANGLES ± 1°

I.I. NUMBER	N/A
PRODUCT SPEC	N/A
WORK INSTRUCTION	N/A
SCALE	NONE
PART NO.	CMF**
DRAWING NO.	01557-04

R	3-16-04	JSP		RELEASED TO PRODUCTION.	01557-04													
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D								

DRAWN BY	JSP	MATERIAL:	MODULE BASE: ABS COUPLER- NICKEL PLATED BRASS
DATE	3-16-04		