



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT P/N | WEIGHT                              |
|-------------|-------------------------------------|
| NKPP48HDV   | 3.86 LB/10 PCS<br>(1745.4 g/10 PCS) |

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:
  - (1) - 48 PORT STAMPING
  - (6) - E POSITION FACEPLATE (ASSEMBLED TO PANEL)
  - (1) - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
  - (1) - SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



|                  |                                |      |   |
|------------------|--------------------------------|------|---|
| MODEL FILENAME   | V01699AA NKPP48HDLASVBLL03.PRT | SIZE | A |
| DRAWING FILENAME | V02479DTE0100100A.PRT          |      |   |

NETKEY 48 PORT HIGH DENSITY MODULAR PATCH PANEL CUSTOMER DRAWING



**PANDUIT**™  
CORP.  
TIMLEY PARK, ILL. 60477



ALL DIMENSIONS ARE GIVEN IN INCHES.  
UNLESS OTHERWISE SPECIFIED.  
DIMENSIONAL TOLERANCES ARE:  
0.001 ± 0.0005 DECIMALS  
0.001 ± 0.0005 ANGLES

DRAWN BY  
JSP

DATE  
3-1-06

STAMPING:  
20 GAGE C.R.S.  
FACEPLATE: ABS

|                  |           |
|------------------|-----------|
| FILE NUMBER      | N/A       |
| PRODUCT SPEC     | N/A       |
| WORK INSTRUCTION | N/A       |
| SCALE            | NONE      |
| PART NO.         | NKPP48HDV |
| DRAWING NO.      | 02479-100 |

|     |        |     |     |                        |           |   |      |     |     |
|-----|--------|-----|-----|------------------------|-----------|---|------|-----|-----|
| REV | DATE   | BY  | CHK | DESCRIPTION            | ECN       | R | CUST | SUP | QTH |
| R   | 3-1-06 | JSP |     | RELEASED TO PRODUCTION | 02479-100 |   |      |     |     |