



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CPPKLA6G24WBL	.85 LB/EACH PC 1376.5 g/EACH PC




.62
[15.9]



NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- PART INCLUDES:
 - 1- INSTRUCTION SHEET
 - 1- 24 PORT ANGLED STAMPING
 - 6- FURNITURE FACEPLATES (OFFPL4)
 - 24- MINI-COM TX6 PLUS JACK MODULE
 - 1- TERMINATION TOOL
 - 1- #12-24 SCREW KIT (INCLUDES 4 SCREWS)
 - 1- M6 SCREW KIT (INCLUDES 4 SCREWS)
 - 6- LABEL
 - 6- LABEL COVER
- PATCH PANELS ACCEPT SNAP-IN MINI-COM MODULES.
- DIMENSIONS IN [] ARE IN METRIC.



DRAWING FILENAME		SIZE
MOD741NO.00133L00A.PRT		A
MINI-COM 24 PORT ANGLED TX6 PLUS MODULAR PATCH PANEL KIT CUSTOMER DRAWING		
PANDUITTM CORP. TINLEY PARK, ILL 60477	U.I. NUMBER	N/A
	PRODUCT SPEC	N/A
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: 1.X1 ±.03 1.XXX1 ±.004 1.XXX1 ±.03 ANGLES ± .5°	WORK INSTRUCTION	N/A
	SCALE	NONE
ON NO ANGLE PROJECTION	PART NO.	CPPKLA6G24WBL
APPROVED BY: JS DATE: 10-5-08 STAMPING: C.P.S. FACEPLATES: A.R.S.	DRAWING NO.	00741-133

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	0-5-08	JAP		RELEASED TO PRODUCTION	00741-133				