THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
PVQ-EPC	0.05 LB EA. 23g EA.

NOTES:
1. CONTACT TECHNICAL SUPPORT FOR APPLICATIONS.
2. CONTACT TECHNICAL SUPPORT FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITHT THIS PART.
3. DIMENSIONS IN BRACKETS ARE IN METRIC.
4. PART INCLUDES:
   (1) PANVIEW IQ EXPANSION PORT CABLE (PVQ-EPC)



MODEL FILENAME: m02676hb_rs485_01.sldprt
DRAWING FILENAME: m02676hb_dc109_00a.slddrw
SIZE: A

PanView iQ EXPANSION PORT CABLE, 0.15m
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 (.XXX) ±.005
(.XX) ±.01 ANGLES ±1°

I. I. NUMBER: N/A
PRODUCT SPEC/ PKG SPEC: N/A
ASSEMBLY METHOD/ TEST METHOD: N/A
SCALE: NONE

DRAWN BY: TCW
DATE: 2/26/08
CHK'D: MJD

REVIEW DRAWING NUMBERS

MAT'L: SEE NOTES ABOVE

PART NO.: PVQ-EPC
DRAWING NO.: 02676-109
Sheet 1 of 1

REV.	DATE	BY	CHK D	DESCRIPTION	ECN	ECN REV	CUS T	SUP	GM BH
R	2/26/08	TCW	MJD	RELEASE TO PRODUCTION	02676-109	MJD	MJD		