




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT PART NUMBER * | WEIGHT<br>lbs/100 pcs<br>(g)/100 pcs | USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS |
|-----------------------|--------------------------------------|------------------------------------------------|
| ABM112-               | WITH ADHESIVE 0.30 (136)             | M, I, S                                        |
|                       | NO ADHESIVE 0.26 (117)               |                                                |



No warranty, expressed or implied, is made by Panduit with respect to adhesive bond performance. Among other things, the conditions under which these mounts may be applied and/or the surface to which they may be applied are beyond Panduit's control.



Adhesive Backing; Pressure Sensitive Adhesive Foam Tape 0.04 (1.0) thick with a protective liner. Mount is designed to support 0.63 lbs. (286g) max. weight on a clean, dry, smooth, grease free surface.

#### NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
- A SUFFIX REPRESENTS RUBBER ADHESIVE  
-AT SUFFIX REPRESENTS ACRYLIC ADHESIVE  
-S6 SUFFIX, NO ADHESIVE; SCREW APPLIED WITH A #6 M3 SCREW
- ADHESIVE MOUNTS ARE SUPPLIED IN STRIPS OF TWO.
- ABM112-A HAS A CONTINUOUS OPERATING TEMPERATURE OF 120°F (49°C). ABM112-AT HAS A CONTINUOUS OPERATING TEMPERATURE OF 180°F (82°C).

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS

G00239F0\_PB\_ABM112\_05

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

ABM112-  
4 WAY MOUNT

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)  
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JAD

MAT'L:

NYLON 6/6

SCALE FULL

DATE 12-17-97

DRAWING NO.

G00239F0

DWG  
A  
SIZE

| 5   | 3/30/06 | JAD |     | DEL ABM30, MOVE TO NEW DWG | G00239F0 | 5 |      |     |  |
|-----|---------|-----|-----|----------------------------|----------|---|------|-----|--|
| REV | DATE    | BY  | CHK | DESCRIPTION                | ECN      | R | CUST | SUP |  |