




NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



ADHESIVE BACKING:
PRESSURE SENSITIVE FOAM TAPE
0.040(1.0) THICK WITH PROTECTIVE
LINER. MOUNT IS DESIGNED TO
SUPPORT 0.13lbs.(59 g) MAX. WEIGHT
ON A CLEAN, DRY, SMOOTH, GREASE-
FREE SURFACE.




ACTUAL SIZE

PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs [g]/100 pcs
ABM1M-A	0.05 [23]

- 1) REMOVE MOUNT FROM PROTECTIVE LINER.
- 2) PLACE IN DESIRED LOCATION.
- 3) APPLY PRESSURE TO TOP SURFACE OF MOUNT.

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR MATERIAL, COLOR, AND PACKAGE SIZE.
2. USE MOUNTS WITH ONLY MINIATURE CABLE TIE CROSS SECTIONS.
3. MOUNTS ARE SUPPLIED IN STRIPS OF FOUR.
4. MOUNT HAS A CONTINUOUS OPERATING TEMPERATURE OF 120° F (49° C).

3	3/23/05	TMSA		REVISED DIMENSION .123 FROM .120 UPDATED LEADER LINE FOR DIMENSION 0.055	680239DC	3			
2	3/29/04	JAD		UPDATE 3D GEOMETRY, AND NOTE 1	680239DC	2			
1	10-26-00	COSM		CHANGED .158 DIMENSION TO REF ADDED NOTE 4	680239DC	1			
R	5/15/98	CJG		INITIAL RELEASE	680239DC	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP		

DIMENSIONS IN BRACKETS ARE METRIC [mm]			
G00239DC_PB_ABM1M_A_03			
		TINLEY PARK, ILLINOIS	
<p style="text-align: center;">ABM1M-A ADHESIVE BACKED MOUNT</p>			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (1.X) ±0.05 (1.3) (1.XXX) ±0.010 (0.25) (1.XX) ±0.02 (0.5) ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY CJB	MAT'L: WHITE NYLON 6/6	SCALE NONE	
DATE 5/15/96		DRAWING NO. G00239DC	QTY A SIZE
CHK'D			