

0.184 (4.67) / 0.164 (4.2) DIA. X 82°
COUNTERSUNK HOLE

REF

0.500
(12.7)


0.550
(14)

REF

0.250
(6.4) REF

PANDUIT PART NO.
LPMS - S

PANDUIT PART NO. *	USE WITH ANY OF THESE CABLE TIE CROSS-SECTIONS	WEIGHT lbs/100pcs. (g)	SCREW SIZE
LPMS-S8	MINIATURE INTERMEDIATE STANDARD	0.102 (46.3)	#8 (M4)



*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX
DESIGNATION FOR PACKAGE SIZE AND COLOR.

2) MATERIAL :

- NATURAL NYLON 6/6
- 0 WEATHER RESISTANT BLACK NYLON 6/6
- 20 HEAT STABILIZED BLACK NYLON 6/6

CAD FILENAME/LAYERS

PANDUIT

LOW PROFILE MOUNT LPMS-S8

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	-----	(.XXX) ±	.020	(.5)
(.XX) ±	-----	ANGLES ±	-----	

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY LG	DATE 11/11/2011
----------------	--------------------

MAT'L:

SEE NOTE 2

	SCALE
--	-------

NONE

DRAWING NO.

GB0239HG

DWG
A
SIZE

I	2/1/06	JAD		ADDED NOTE 2, 0.74 (REF) WAS 0.75, 0.184/0.164 WAS 0.180/0.164	GB0239HG	I				
R	6-6-01	LGG		REVISED DRAWING FROM SS-5783-A-RV 3 TO NEW DRAWING NUMBER	GB0239HG	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		