


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOMINAL DUCT SIZE (W)	C in (mm)	TC in (mm)	HC in (mm)	HC TOL. in (mm)
.5	.69 (17.5)	.040 (1.0)	.190 (4.8)	±.120 (3.1)
1	1.25 (31.8)	.060 (1.5)	.290 (7.4)	±.100 (2.5)
1.5	1.75 (44.5)	"	"	"
2	2.25 (57.2)	"	"	"
2.5	2.75 (69.9)	"	.310 (7.9)	"
3	3.25 (82.6)	.085 (1.6)	.300 (7.6)	±.120 (3.1)
4	4.25 (108.0)	"	"	"



△ PART NO. SYSTEM COVER EXAMPLE  
 NC 2 WH 6  
 TYPE WIDTH COLOR LENGTH (L) △

NOTES  
 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.  
 2. DIMENSIONS IN PARENTHESIS ARE IN METRIC.

CAD FILE NAME/LAYERS D34518BA\_NOR\_COVER\_02A

# PANDUIT

CORP. TINLEY PARK, ILLINOIS

WIRING DUCT COVER  
 FOR DUCT TYPES "NS", "NE"  
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
 ( .X ) : ANGLES :  
 ( .XX ) :

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: DW  
 DATE: 12-8-93  
 CHK'D: CEF

MAT'L: MODIFIED POLYPHENYLENE OXIDE △

SCALE: NONE

DRAWING NO. 34518-27

DWG SIZE A

REV	DATE	BY	CHK	ECN	R	CUST	SUP	DESCRIPTION
1	8-16-01	JCST	JKG	34518-27	JKG	JKG		
R	5-27-94	DW	CEF	34518-27	CEF	CEF		RELEASED TO PRODUCTION.