


FIBER OPTIC 900 μ m BUFFERED LC PIGTAIL							
PANDUIT PART NO.	CABLE				CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5B10-NM*	RISER (OFNR)	50/125 μ m	SIMPLEX 900 μ m BUFFERED FIBER	BLUE	0.25dB	20dB	BLACK
F6B10-NM*		62.5/125 μ m					ELECTRIC IVORY
FXB10-NM*		10GbE OM3			0.25dB	26dB	AQUA
FXOB10-NM*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZB10-NM*		10GbE OM4			0.25dB	26dB	AQUA
FZOB10-NM*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9B10-NM*		9/125 μ m OS1			0.35dB	55dB	BLUE

* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC 900 μ m BUFFERED LC PIGTAIL CUSTOMER DRAWING		
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477	DRAWING FILENAME M02779CZ_DC/01A	
											SCALE NONE	
										 THIRD ANGLE PROJECTION	PART NO. SEE TABLE	
R	09-09-09	EFK		RELEASED TO PRODUCTION	02779-63						DRAWING NO. 02779-63 SHEET 2 OF 2	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH		SIZE A	