




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FJ OPTI-PLUG TO ST FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				FJ OPTI-PLUG			ST CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	COLOR
F5D6P-2M*Y	RISER (OFNR)	50/125um OM2	DUPLICATE 3.0mm ZIPCORD	ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	METALLIC FINISH
F6D6P-2M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	METALLIC FINISH
F9D6P-2M*Y		9/125um OS1		YELLOW	0.75dB	55dB	BLUE	0.75dB	55dB	METALLIC FINISH

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

												FIBER OPTIC PATCH CORD FJ OPTI-PLUG TO ST CONFIGURATION CUSTOMER DRAWING	
													
													ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES
												DRAWING FILENAME M02779BJ_DC_00A.prt	
												SCALE NONE	
												PART NO. SEE TABLE	
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-16							DRAWING NO. 02779-16 (SHT. 2 of 2)	
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH	CHK'D	SIZE A	