THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

GRIP SPAN:
1.5" (38.1 mm)
FULLY CLOSED

6.5" (165.0 mm)
FULLY OPEN

FULL STROKE COMPELLING DEVICE

MANUAL RACHET

"P" CODE DIE DETAIL

REPLACEABLE DIE SET
SEE SHEET 2



.260" (6.6 mm)
FULLY CLOSED HANDLE GAP

2.96" (75.3) mm

1.60" (40.6 mm)

8.66 " (220.0 mm)

SEE SHEET 2 FOR SPECIFICATIONS

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	COST	SUP
00	9.05.01	JPW	RLO	RELEASED*RPLCS TD23993C01	3985	RFL	

PANDUIT CORP. TINLEY PARK, ILLINOIS

FCRP5 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± ..... (.XXX) ± .....
(.XX) ± ..... ANGLES ± .....

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES. THIRD ANGLE PROJECTION.

DRAWN: DS / JW
DATE: 9.05.01
CHK'D: RLO

MAT'L:

SHEET 1 OF 2

SCALE: NONE

DRAWING NO.: TP24600A01

SIZE: A

ASIZETEMP (DWG) WORK

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES UNLESS OTHERWISE SPECIFIED:

PANDUIT TOOL NUMBER **FCRP5** FIBER OPTIC HAND TOOL CRIMPS .048, .100, .128, .151, AND .190 HEX SIZES.

TOOL FEATURES:
CUSHION HAND GRIPS
CONTROLLED CYCLE
REPLACEABLE DIE SET PART NUMBER = **CD-FCRP5**
TOOL WEIGHT = 1.20 LBS / 30.5 Kg

ADDITIONAL DIMENSIONS:

.96" (24.4 mm) MAXIMUM HANDLE WIDTH
.93" (23.5 mm) MAXIMUM TOOL NOSE WIDTH

SEE SHEET 1 FOR TOOL DIMENSIONS

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP
00	9.05.01			SEE SHEET 1 FOR RELATED INFO	3985	RFL	

PANDUIT CORP. TINLEY PARK, ILLINOIS

FCRP5 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XX) ± (.XXX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION.

DRAWN BY: DS/JW
DATE: 9.05.01
CHK'D: RLO
MAT'L:
SHEET 2 OF 2
SCALE: NONE
DRAWING NO.: TP24600A01
SIZE: A

ASIZETEMP (DWG) WORK