




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
FJPKGU	.47 LB/10 PCS (214.5 g/10 PCS)



NOTES:


1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



UNIVERSAL POLISHING PUCK
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



THIRD ANGLE
PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES,
UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWING FILENAME
M00017CL_DC_03A.prt
SCALE
NONE

DRAWN BY
JsP

MAT'L:
STAINLESS
STEEL

PART NO.
FJPKGU

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	04-18-05	MYW		RELEASED TO PRODUCTION.	00017-23				

DATE
5-8-98

STAINLESS
STEEL

DRAWING NO.
00017-23

CHK'D
FJD

SIZE
A