





PORTS → 1 3 5 7 9 11
2 4 6 8 10 12


DUSTCAPS NOT SHOWN
IN THIS VIEW FOR
CLARITY



PANDUIT PART NUMBER	DESCRIPTION
FQ6-12-10	62.5/125 OM1 MULTIMODE 12 FIBER LC TO MTP CASSETTE
FQ5-12-10	50/125 OM2 MULTIMODE 12 FIBER LC TO MTP CASSETTE
FQX-12-10	50/125 OM3 MULTIMODE 12 FIBER LC TO MTP CASSETTE
FQX0-12-10	OPTIMIZED 50/125 OM3 MULTIMODE 12 FIBER LC TO MTP CASSETTE
FQZ-12-10	50/125 OM4 MULTIMODE 12 FIBER LC TO MTP CASSETTE
FQZ0-12-10	OPTIMIZED 50/125 OM4 MULTIMODE 12 FIBER LC TO MTP CASSETTE
FQ9-12-10	9/125 OS1/OS2 SINGLEMODE 12 FIBER LC TO MTP CASSETTE

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
A. MODULE MATERIAL: PLASTIC
B. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 2.4oz (69.0g)
5. DIMENSIONS IN BRACKETS ARE METRIC

										QUICKNET SFQ SERIES CASSETTE 12 FIBER, LC TO MTP CONFIGURATION CUSTOMER DRAWING				
											 TM CORP. TINLEY PARK, ILL 60477			
											DRAWING FILENAME MO2947ZD_DC/01A			
											SCALE NONE			
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES			
											SCALE NONE			
										DRAWN BY EFK	REVIEW DRAWING NUMBERS		PART NO. FQ**-12-10	
										DATE 09-19-08			DRAWING NO. 02947-30	
										CHK'D WMA			SIZE A	
2	09-13-11	MC	MTV	RELEASED TO PRODUCTION		02947-30	MTV	CVM						
REV	DATE	BY	CHK	DESCRIPTION		ECN	- R	CUST	SUP	OTH				