


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.
3. KIT CONTAINS (KIT INCLUDED WITH ENCLOSURE):
 - 5 - PAN-TY CABLE TIES
 - 1 - GROUNDING LUG
 - 1 - HEX NUT
 - 1 - FIBER CAUTION LABEL
 - 1 - FIBER LASER BEAM WARNING LABEL
 - 2 - BAGS OF #12 - 24 X .5" SCREWS
 - 1 - 24" LENGTH OF SPIRAL WRAP
 - 8 - SADDLE MOUNT
 - 1 - BAG OF #10 - 32 X .3125" PHILLIPS PAN-HEAD SCREWS
 - 10 - VELCRO CABLE TIES
4. ENCLOSURE FITS INTO A 19" OR 23" RACK SPACE.
5. ENCLOSURE CAN BE MOUNTED FLUSH OR PROJECTED IN RACK OPENING.
6. MATERIAL: 16 GAUGE GALVANNEALED C.R.S. HOUSING: 16 GAUGE GALVANNEALED C.R.S. FRONT AND BACK COVER: STEEL



CAD FILENAME/LAYERS

M00406AA_DC_03A.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

FIBER ENCLOSURE, 4 RACK
SPACE SPLICE (FRME144SBL)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±.010 (.3)
(.XX) ±.03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JBA
DATE 3-24-99
CHECKED BY

MAT'L:
SEE NOTES

SCALE
NONE

DWG
00406-21
SHEET 2 OF 2
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
R	3-24-99	JBA		SEE SHEET 1 OF 2 FOR CURRENT REVISIONS.	00406-21			

