



900um BUFFERED DUPLEX FIBER OPTIC FJ-JACK PIGTAIL							
PANDUIT PART NO.	BUFFERED FIBER				FJ-JACK		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR
FXB6J-NM*Y	NO FLAME RATING	10GbE 50/125um OM3	2	BLUE & ORANGE	0.30dB	26dB	ELECTRIC IVORY
F5B6J-NM*Y		50/125um OM2	2	BLUE & ORANGE	0.30dB	20dB	ELECTRIC IVORY
F6B6J-NM*Y		62.5/125um OM1	2	BLUE & ORANGE	0.30dB	20dB	ELECTRIC IVORY
F9B6J-NM*Y		9/125um OS1	2	BLUE & ORANGE	0.75dB	55dB	BLUE

* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

										900um BUFFERED DUPLEX FIBER OPTIC FJ-JACK PIGTAIL CUSTOMER DRAWING		
											PANDUIT TM CORP. TINLEY PARK, ILL 60477	
											ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (1.X) (1.XX) ±.03 (0.8) ANGLES (1.XXX) ±.010 (0.3)	DRAWING FILENAME M02779CC_DC_00A.prt SCALE NONE
										 THIRD ANGLE PROJECTION	DRAWN BY MC DATE 05-22-07 CHK'D	REVIEW DRAWING NUMBERS PART NO. SEE TABLE DRAWING NO. 02779-33 (SHT. 2 of 2)
R	06-04-07	MC		RELEASED TO PRODUCTION	02779-33							SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH			