



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP | OTH | FIBER OPTIC PATCH CORD DUPLIX ST TO ST CONFIGURATION CUSTOMER DRAWING | |
|-----|----------|----|-----|------------------------|----------|---|------|-----|-----|--|--|
| | | | | | | | | | |  PANDUIT TM CORP. TINLEY PARK, ILL 60477 | |
| | | | | | | | | | | | ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (0.8) ANGLES (.XXX) ±.010 (0.3) |
| | | | | | | | | | | DRAWING FILENAME M02779BE_DC_00A.prt SCALE NONE | |
| | | | | | | | | | | DRAWN BY MC DATE 04-27-07 CHK'D | |
| | | | | | | | | | | REVIEW DRAWING NUMBERS PART NO. SEE TABLE, SHT. 2 DRAWING NO. 02779-13 (SHT. 1 of 2) | |
| | | | | | | | | | | SIZE A | |
| R | 06-05-07 | MC | | RELEASED TO PRODUCTION | 02779-13 | | | | | | |

| DUPLEX ST TO ST FIBER OPTIC PATCH CORD | | | | | | | |
|--|--|------------------------|----------------------------|--------|--------------|---------|--------------------|
| PANDUIT PART NO. | CABLE | | | | ST CONNECTOR | | |
| | RATING | FIBER TYPE | COUNT | COLOR | MAX. IL | MIN. RL | COLOR |
| FXD2-2M*Y | RISER (OFNR) | 10 GbE 50/125um OM3 | DUPLEX 3.0mm ZIPCORD | AQUA | 0.30dB | 26dB | METALLIC FINISH |
| F5D2-2M*Y | | 50/125um OM2 | | ORANGE | 0.30dB | 20dB | METALLIC FINISH |
| F6D2-2M*Y | | 62.5/125um OM1 | | ORANGE | 0.30dB | 20dB | METALLIC FINISH |
| F9D2-2M*Y | | 9/125um OS1 | | YELLOW | 0.75dB | 55dB | METALLIC FINISH |
| FXPD2-2M* | PLENUM (OFNP) | 10 GbE 50/125um OM3 | DUPLEX 3.0mm ZIPCORD | AQUA | 0.30dB | 26dB | METALLIC FINISH |
| F5PD2-2M* | | 50/125um OM2 | | ORANGE | 0.30dB | 20dB | METALLIC FINISH |
| F6PD2-2M* | | 62.5/125um OM1 | | ORANGE | 0.30dB | 20dB | METALLIC FINISH |
| F9PD2-2M* | | 9/125um OS1 | | YELLOW | 0.75dB | 55dB | METALLIC FINISH |
| FXLD2-2M* | LOW SMOKE ZERO HALOGEN (LSZH) IEC | 10 GbE 50/125um OM3 | DUPLEX 3.0mm ZIPCORD | AQUA | 0.30dB | 26dB | METALLIC FINISH |
| F5LD2-2M* | | 50/125um OM2 | | ORANGE | 0.30dB | 20dB | METALLIC FINISH |
| F6LD2-2M* | | 62.5/125um OM1 | | ORANGE | 0.30dB | 20dB | METALLIC FINISH |
| F9LD2-2M* | | 9/125um OS1 | | YELLOW | 0.75dB | 55dB | METALLIC FINISH |

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

| | | | | | | | | | | | | | | | |
|-----|----------|----|-----|------------------------|----------|---|------|-----|-----|---|--|--|--|--|--|
| | | | | | | | | | | FIBER OPTIC PATCH CORD DUPLEX ST TO ST CONFIGURATION CUSTOMER DRAWING | | | | | |
| | | | | | | | | | |  PANDUIT ™ CORP. TINLEY PARK, ILL 60477 | | | | | |
| | | | | | | | | | |  THIRD ANGLE PROJECTION | | ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.01 (.XX) ±.03 (.8) ANGLES | | DRAWING FILENAME MO2779BE_DC_00A.prt SCALE NONE | |
| | | | | | | | | | | DRAWN BY MC | | REVIEW DRAWING NUMBERS | | PART NO. SEE TABLE | |
| | | | | | | | | | | DATE 04-27-07 | | DRAWING NO. 02779-13 | | SIZE A | |
| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP | OTH | CHK'D | | | | | |
| R | 06-05-07 | MC | | RELEASED TO PRODUCTION | 02779-13 | | | | | | | | | | |