



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITIES.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



										FIBER OPTIC PATCH CORD DUPLEX ST TO SC CONFIGURATION CUSTOMER DRAWING			
										 <b>PANDUIT</b> <sup>TM</sup> CORP. TINLEY PARK, ILL 60477			
										ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.		DRAWING FILENAME M02779BD_DC_00A.prt	
										DIMENSIONAL TOLERANCES ARE: (.X) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES		SCALE NONE	
										THIRD ANGLE PROJECTION		PART NO. SEE TABLE, SHT. 2	
										DRAWN BY MC		REVIEW DRAWING NUMBERS	
										DATE 04-27-07		DRAWING NO. 02779-12	
										CHECK'D		(SHT. 1 of 2)	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH			SIZE <b>A</b>	
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-12								

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX ST TO SC FIBER OPTIC PATCH CORD

PANDUIT PART NO.	CABLE				ST CONNECTOR			SC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	COLOR	MAX. IL	MIN. RL	COLOR
FXD2-3M*Y	RISER (OFNR)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH	0.30dB	26dB	ELECTRIC IVORY
F5D2-3M*Y		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F6D2-3M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F9D2-3M*Y		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH	0.75dB	55dB	BLUE
FYPD2-3M*	PLENUM (OFNP)	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH	0.30dB	26dB	ELECTRIC IVORY
F5PD2-3M*		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F6PD2-3M*		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F9PD2-3M*		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH	0.75dB	55dB	BLUE
FXLD2-3M*	LOW SMOKE ZERO HALOGEN (LSZH) IEC	10 GbE 50/125um OM3	DUPLEX 3.0mm ZIPCORD	AQUA	0.30dB	26dB	METALLIC FINISH	0.30dB	26dB	ELECTRIC IVORY
F5LD2-3M*		50/125um OM2		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F6LD2-3M*		62.5/125um OM1		ORANGE	0.30dB	20dB	METALLIC FINISH	0.30dB	20dB	ELECTRIC IVORY
F9LD2-3M*		9/125um OS1		YELLOW	0.75dB	55dB	METALLIC FINISH	0.75dB	55dB	BLUE

\* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX ST TO SC CONFIGURATION CUSTOMER DRAWING					
										 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477					
										 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03   (.XXX) ±.010   (0.3)		DRAWING FILENAME M02779BD_DC_00A.prt	
										DRAWN BY MC		REVIEW DRAWING NUMBERS		PART NO. SEE TABLE	
R	06-05-07	MC	RELEASED TO PRODUCTION				02779-12			DATE	04-27-07	DRAWING NO. 02779-12		SIZE	A
REV	DATE	BY	CHK	DESCRIPTION				ECN - R	CUST	SUP	OTH	(SHT. 2 of 2)			