



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF RANDUIT CORP.



NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANOUT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANOUT'S CONTROL.

PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs (g/100 pcs)	USE WITH THESE CABLE TIE CROSS-SECTIONS
ABMS-A	0.42 (169)	M, J, S

TO APPLY ADHESIVE MOUNT:
1) REMOVE PROTECTIVE LINER.
2) PLACE IN DESIRED LOCATION.
3) APPLY PRESSURE TO TOP
SURFACE OF MOUNT.



ADHESIVE BACKING:
PRESSURE SENSITIVE FOAM TAPE
0.04 (1.0) THICK WITH PROTECTIVE
LINER. MOUNT IS DESIGNED TO
SUPPORT 0.8 lb. (27g.) MAX. WEIGHT
ON A CLEAN, DRY, SMOOTH, GREASE-FREE
SURFACE.

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE.
- 2) MOUNTS PROVIDED IN STRIPS OF TWO FOR EASY REMOVAL OF PROTECTIVE LINER.
- 3) MOUNTS WILL BE ORIENTED IN LINE WITH, OR 90° FROM EACH OTHER AS ILLUSTRATED ABOVE.

DIMENSIONS IN BRACKETS ARE METRIC (mm)

000239GE CC ABMS 03

PANDUIT

CORP. TIMLEY PARK, ILLINOIS

ABMS-A
ADHESIVE BACKED MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
1.X) ± 0.05 1.3) 1.7XXX) ± 0.010 10.25;
1.3XX) ± 0.02 [0.5] ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, ROUND UNLESS INDICATED.

DATE	NAME	MARK
10/10/10	JOHN	85

2-11-66

NYLON 6/6

NCNE

DATE: _____

GB0239GE

29